



FCIconnect.com

Copyright FCI

PRODUCT NUMBER

71991-YXXXLF

WHEN NEEDED, SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 6.

OPTIONAL LETTER

H: HIGH TEMPERATURE PRODUCT.

NUMBER OF POSITIONS PER ROW: 02 TO 50.

PLATING CODE

3= 0.76µm GOLD ON CONTACT AREA.

3.81µm TIN-LEAD ON TAIL.

4= 5µm TIN-LEAD ON CONTACT AREA.

3.81µm TIN-LEAD ON TAIL.

8= 0.38µm GOLD ON CONTACT AREA.

3.81µm TIN-LEAD ON TAIL.

WHEN SUFFIX "LF" IS REQUIRED, 2µm MIN MATTE
TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.

NOTES:

- 1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED
FLAME RETARDANT PER UL 94 V-0
LOW TEMPERATURE: COLOR BLUE
HIGH TEMPERATURE: COLOR GREY.
- 2 - TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 - 2 UP TO 50 POSITIONS PRODUCT PACKED IN TUBE.
- 4 - TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW
EXAMPLE: 8 POS: $(N \times 2.54) - 0.08 = 20.24$ mm
- 5 - RECOMMENDED IR PROFIL PER TA 842.
- 6 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:




- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.



b - MANUFACTURING PROCESS COMPATIBILITY


- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C ±5°C SOLDER BATH TEMPERATURE FOR
5 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.6mm MIN THICK CIRCUIT BOARD.

c - LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-22-008

mat'l. code SEE NOTES				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family DUBOX					
Ltr ecn na dr date				tolerances unless otherwise specified						title BtB RECEPT. VERT DR TMT					
R F10132 DLE 01.02.06				angles linear		±0.3									
S F04.0347 DLE 04.09.27															
T F06-0137 DLE 06.02.27				±2°				scale 5:1		dwg no sheet 1 of 2 size 71991 A3					
U F06-0204 DLE 06.06.20				dr D LEGRAND		04.09.27									
V F06-0323 DLE 06.11.21				enr P NIZZI		04.09.27									
				chr D LEGRAND		04.09.27									
P F10110 GCO 01.01.16				appd P NZ		04.09.27				type CUSTOMER Drawing					
sheet index		revision		V B											
		sheet		1 2											



mat'l. code				surface		tolerance		projection		product family	
SEE SHEET 1				ISO 1302 ✓		ISO 406 ISO 1101		⌀		DUBOX	
ltr	ecn no	dr	date	tolerances unless otherwise specified		±0.3		mm		title	
A	F04-0347	DLE	04.09.27	angles				⌀		BtB RECEIPT.	
B	F06-0204	DLE	06.06.20	linear				↔		VERT DR TMT	
				±2°				scale 5:1		dwg no	
				dr		D LEGRAND		04.09.27		sheet 2 of 2	
				engr		P NIZZI		04.09.27		size	
				chr		D LE		04.09.27		A4	
				appd		P NZ		04.09.27		type	
										CUSTOMER	
										Drawing	
sheet index	revision										
	sheet										