


DATA SHEET
Low Distortion GaAs Power FET

- **NON-HERMETIC LOW COST CERAMIC 70mil PACKAGE**
- **+22.0dBm TYPICAL OUTPUT POWER**
- **8.0dB TYPICAL POWER GAIN AT 12GHz**
- **0.3 X 400 MICRON RECESSED “MUSHROOM” GATE**
- **Si₃N₄ PASSIVATION**
- **ADVANCED EPITAXIAL DOPING PROFILE PROVIDES HIGH POWER EFFICIENCY, LINEARITY AND RELIABILITY**



All Dimensions In mils.

ELECTRICAL CHARACTERISTICS (T_a = 25 °C)

SYMBOLS	PARAMETERS/TEST CONDITIONS	MIN	TYP	MAX	UNIT
P_{1dB}	Output Power at 1dB Compression V _{ds} =6V, I _{ds} =50% I _{dss} f=12GHz f=18GHz	20.0	22.0 22.0		dBm
G_{1dB}	Gain at 1dB Compression V _{ds} =6V, I _{ds} =50% I _{dss} f=12GHz f=18GHz	6.5	8.0 5.0		dB
PAE	Gain at 1dB Compression V _{ds} =6V, I _{ds} =50% I _{dss} f=12GHz		33		%
I_{dss}	Saturated Drain Current V _{ds} =3V, V _{gs} =0V	60	105	160	mA
G_m	Transconductance V _{ds} =3V, V _{gs} =0V	45	60		mS
V_p	Pinch-off Voltage V _{ds} =3V, I _{ds} =1.0 mA		-2.0	-3.5	V
BV_{gd}	Drain Breakdown Voltage I _{gd} =1.0mA	-10	-15		V
BV_{gs}	Source Breakdown Voltage I _{gs} =1.0mA	-6	-14		V
R_{th}	Thermal Resistance		250*		°C/W

* Overall R_{th} depends on case mounting.

MAXIMUM RATINGS AT 25°C

SYMBOLS	PARAMETERS	ABSOLUTE ¹	CONTINUOUS ²
V_{ds}	Drain-Source Voltage	10V	6V
V_{gs}	Gate-Source Voltage	-6V	-4V
I_{ds}	Drain Current	I _{dss}	75mA
I_{gsf}	Forward Gate Current	10mA	1.5mA
P_{in}	Input Power	21dBm	@ 3dB Compression
T_{ch}	Channel Temperature	175°C	150 °C
T_{stg}	Storage Temperature	-65/175°C	-65/150 °C
P_t	Total Power Dissipation	550mW	445mW

Note: 1 Exceeding any of the above ratings may result in permanent damage.

2. Exceeding any of the above ratings may reduce MTTF below design goals.

Excelics Semiconductor, Inc., 2908 Scott Blvd., Santa Clara, CA 95054

Phone: (408) 970-8664 Fax: (408) 970-8998 Web Site: www.excelics.com

EFA040A-70

DATA SHEET

Low Distortion GaAs Power FET

S-PARAMETERS

6V, 1/2 Idss

FREQ (GHz)	--- S11 ---		--- S21 ---		--- S12 ---		--- S22 ---	
	MAG	ANG	MAG	ANG	MAG	ANG	MAG	ANG
1.0	0.971	-30.2	4.747	154.4	0.021	72.3	0.714	-14.0
2.0	0.908	-59.1	4.348	130.0	0.037	55.5	0.681	-29.1
3.0	0.842	-84.8	3.860	108.4	0.047	42.9	0.651	-42.1
4.0	0.782	-109.8	3.516	88.8	0.052	33.0	0.626	-52.4
5.0	0.726	-133.4	3.212	70.4	0.055	24.9	0.592	-62.1
6.0	0.686	-152.0	2.939	53.7	0.055	20.6	0.558	-74.9
7.0	0.652	-172.6	2.687	37.1	0.055	16.8	0.543	-86.4
8.0	0.626	167.7	2.492	21.4	0.054	16.2	0.517	-96.6
9.0	0.631	140.1	2.292	4.2	0.057	17.8	0.511	-104.6
10.0	0.652	117.8	2.096	-12.5	0.063	14.5	0.497	-118.4
11.0	0.659	103.2	2.002	-28.6	0.073	9.8	0.485	-137.9
12.0	0.681	86.0	1.899	-45.5	0.083	2.8	0.480	-157.0
13.0	0.739	69.3	1.706	-61.4	0.088	-6.5	0.463	-173.7
14.0	0.776	55.3	1.513	-76.5	0.091	-16.1	0.465	168.8
15.0	0.787	41.1	1.400	-94.1	0.095	-29.4	0.498	144.8
16.0	0.798	25.7	1.269	-113.2	0.094	-44.6	0.518	120.3
17.0	0.789	15.5	1.103	-126.3	0.092	-50.4	0.516	105.9
18.0	0.803	7.3	1.043	-138.6	0.101	-67.9	0.574	93.1
19.0	0.821	-7.7	0.928	-155.5	0.085	-83.5	0.604	75.9
20.0	0.846	-19.7	0.854	-171.7	0.080	-98.6	0.657	59.9
21.0	0.829	-28.2	0.801	173.6	0.076	-113.9	0.654	47.1
22.0	0.795	-39.9	0.760	160.1	0.076	-129.4	0.650	38.6
23.0	0.808	-56.6	0.695	142.7	0.075	-147.4	0.629	20.9
24.0	0.819	-69.7	0.633	124.1	0.078	-168.0	0.617	0.1
25.0	0.756	-84.3	0.617	107.6	0.089	176.3	0.618	-14.7
26.0	0.754	-103.8	0.634	90.8	0.117	161.8	0.599	-30.8