

Home: Crimp Housings >

Part Number: 48106-0715

2.00mm Pitch, Wire-to-Board, 7 Circuits, Crimp Housing, Green

Image not available

Status:OBSELETE

Replacement:Contact Molex

Series:48106

Category:Crimp Housings

CHECK DISTRIBUTOR INVENTORY

Add to My Parts

Email this page

Go to Part Detail▼

Series image - Reference only

Mates With Part(s):
48107, 48148

Use With Part(s):
48105

Product Environmental Compliance

EU ELV:Product not active

EU RoHS:Product not active

EU RoHS Phthalates:Product not active

China RoHS:

REACH SVHC:Product not active

Low-Halogen Status:Product not active

PDF

EU RoHS Certificate of Compliance (PDF)

PDF

Multiple Part Product Compliance Statements

EU RoHS, REACH SVHC, & Low-Halogen

PDF

Multiple Part Industry Compliance Documents

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

Application Tooling

FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

Check our list of old tooling that used to be available for this part

Questions on Product Environmental Compliance? EmailProductCompliance@molex.com

Request Molex's CMRT from conflictminerals@molex.com

Part Detail

COLLAPSE ALL

General

Status	Obsolete
Category	Crimp Housings
Series	48106
Application	Signal
Product Name	N/A
UPC	822348539352

Physical

Circuits (maximum)	7
Flammability	94V-0
Gender	Receptacle
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-25°C to +85°C

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	2.0A
-------------------------------	------

Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number. Click here to visit the UL Database

CSA	LR19980
UL	E29179

PRODUCTS

Antennas

Application Tooling

Cable Assemblies

Connected Lighting

Connectors

Copper Flex

Electrical Products

Industrial Automation

Membrane Switches

Optical Solutions

Printed Electronic Solutions

QUICK LINKS

Company Information

Contact Molex

Cross-Reference

Koch Industries

Industries

Investor Relations

Literature

Molex Racing

Press Room / Press Releases

Product Index

Sitemap

Terms & Conditions

RESOURCES

Supply Chain Transparency

Business Continuity

Compliance

ecocare

Feedback | Help

Jobs

Legal | Trademarks

Mobile Site

Supplier Portal

Privacy Policy

Tradeshows

STAY CONNECTED

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2017