

Internally-compensated dual low noise operational amplifier

NE/SE5532/5532A

DESCRIPTION

The 5532 is a dual high-performance low noise operational amplifier. Compared to most of the standard operational amplifiers, such as the 1458, it shows better noise performance, improved output drive capability and considerably higher small-signal and power bandwidths.

This makes the device especially suitable for application in high-quality and professional audio equipment, instrumentation and control circuits, and telephone channel amplifiers. The op amp is internally compensated for gains equal to one. If very low noise is of prime importance, it is recommended that the 5532A version be used because it has guaranteed noise voltage specifications.

FEATURES

- Small-signal bandwidth: 10MHz
- Output drive capability: 600Ω, 10V_{RMS}
- Input noise voltage: 5nV/√Hz (typical)
- DC voltage gain: 50000
- AC voltage gain: 2200 at 10kHz
- Power bandwidth: 140kHz
- Slew rate: 9V/μs
- Large supply voltage range: ±3 to ±20V
- Compensated for unity gain

PIN CONFIGURATIONS




Figure 1. Pin Configurations

ORDERING INFORMATION

DESCRIPTION	TEMPERATURE RANGE	ORDER CODE	DWG #
8-Pin Plastic Dual In-Line Package (DIP)	0 to 70°C	NE5532N	SOT97-1
8-Pin Ceramic Dual In-Line Package (CERDIP)	0 to 70°C	NE5532FE	0580A
8-Pin Plastic Dual In-Line Package (DIP)	0 to 70°C	NE5532AN	SOT97-1
8-Pin Ceramic Dual In-Line Package (CERDIP)	0 to 70°C	NE5532AF	0580A
8-Pin Ceramic Dual In-Line Package (CERDIP)	-55°C to +125°C	SE5532FE	0580A
8-Pin Ceramic Dual In-Line Package (CERDIP)	-55°C to +125°C	SE5532AF	0580A
8-Pin Small Outline Package (SO)	0 to 70°C	NE5532AD8	SOT96-1
8-Pin Small Outline Package (SO)	-55°C to +125°C	SE5532AD8	SOT96-1
8-Pin Small Outline Package (SO)	0 to 70°C	NE5532D8	SOT96-1
8-Pin Small Outline Package (SO)	-55°C to +125°C	SE5532D8	SOT96-1
16-Pin Plastic Small Outline Large (SOL) Package	0 to 70°C	NE5532D	SOT162-1
16-Pin Plastic Dual In-Line Package (DIP)	-55°C to +125°C	SE5532N	SOT38-4

Internally-compensated dual low noise operational amplifier

NE/SE5532/5532A

EQUIVALENT SCHEMATIC (EACH AMPLIFIER)




Figure 2. Equivalent Schematic (Each Amplifier)

ABSOLUTE MAXIMUM RATINGS

SYMBOL	PARAMETER	RATING	UNIT
V _S	Supply voltage	±22	V
V _{IN}	Input voltage	±V _{SUPPLY}	V
V _{DIFF}	Differential input voltage ¹	±0.5	V
T _A	Operating temperature range	0 to 70	°C
		-55 to +125	°C
T _{STG}	Storage temperature	-65 to +150	°C
T _J	Junction temperature	150	°C
P _D	Maximum power dissipation,		
	T _A =25°C (still-air) ²		
	8 N package	1200	mW
	8 FE package	1000	mW
T _{SOLD}	Lead soldering temperature (10sec max)	1200	mW
		300	°C

NOTES:

1. Diodes protect the inputs against over-voltage. Therefore, unless current-limiting resistors are used, large currents will flow if the differential input voltage exceeds 0.6V. Maximum current should be limited to ±10mA.
2. Thermal resistances of the above packages are as follows:

N package at 100°C/W
F package at 135°C/W
D package at 105°C/W

Internally-compensated dual low noise operational amplifier

NE/SE5532/5532A

DC ELECTRICAL CHARACTERISTICS

T_A=25°C V_S=±15V, unless otherwise specified. 1, 2, 3

SYMBOL	PARAMETER	TEST CONDITIONS	SE5532/5532A			NE5532/5532A			UNIT
			Min	Typ	Max	Min	Typ	Max	
V _{OS}	Offset voltage	Over temperature		0.5	2		0.5	4	mV
ΔV _{OS} /ΔT				5	3		5	5	mV/°C
I _{OS}	Offset current				100		10	150	nA
ΔI _{OS} /ΔT		Over temperature		200	200		200	200	nA/°C
I _B	Input current	Over temperature		200	400		200	800	nA
ΔI _B /ΔT				5	700		5	1000	nA/°C
I _{CC}	Supply current			8	10.5		8	16	mA
		Over temperature			13				mA
V _{CM}	Common-mode input range		±12	±13		±12	±13		V
CMRR	Common-mode rejection ratio		80	100		70	100		dB
PSRR	Power supply rejection ratio			10	50		10	100	μV/V
A _{VOL}	Large-signal voltage gain	R _L ≥2kΩ, V _O =±10V Over temperature R _L ≥600Ω, V _O =±10V Over temperature	50 25 40 20	100 50		25 15 15 10	100 50		V/mV V/mV V/mV V/mV
V _{OUT}	Output swing	R _L ≥600Ω Over temperature R _L ≥600Ω, V _S =±18V Over temperature R _L ≥2kΩ Over temperature	±12 ±10 ±15 ±12 ±13 ±12	±13 ±12 ±16 ±14 ±13.5 ±12.5		±12 ±10 ±15 ±12 ±13 ±10	±13 ±12 ±16 ±14 ±13.5 ±12.5		V
R _{IN}	Input resistance		30	300		30	300		kΩ
I _{SC}	Output short circuit current		10	38	60	10	38	60	mA

NOTES:

- Diodes protect the inputs against overvoltage. Therefore, unless current-limiting resistors are used, large currents will flow if the differential input voltage exceeds 0.6V. Maximum current should be limited to ±10mA.
- For operation at elevated temperature, derate packages based on the package thermal resistance.
- Output may be shorted to ground at V_S=±15V, T_A=25°C Temperature and/or supply voltages must be limited to ensure dissipation rating is not exceeded.

AC ELECTRICAL CHARACTERISTICS

T_A=25°C V_S=±15V, unless otherwise specified.

SYMBOL	PARAMETER	TEST CONDITIONS	NE/SE5532/5532A			UNIT
			Min	Typ	Max	
R _{OUT}	Output resistance	A _V =30dB Closed-loop f=10kHz, R _L =600Ω		0.3		Ω
	Overshoot	Voltage-follower V _{IN} =100mV _{P-P} C _L =100pF, R _L =600Ω		10		%
A _V	Gain	f=10kHz		2.2		V/mV
GBW	Gain bandwidth product	C _L =100pF, R _L =600Ω		10		MHz
SR	Slew rate			9		V/μs
	Power bandwidth	V _{OUT} =±10V V _{OUT} =±14V, R _L =600Ω, V _{CC} =±18V		140 100		kHz kHz

Internally-compensated dual low noise operational amplifier


NE/SE5532/5532A

ELECTRICAL CHARACTERISTICS

T_A=25°C V_S=±15V, unless otherwise specified.

SYMBOL	PARAMETER	TEST CONDITIONS	NE/SE5532			NE/SE5532A			UNIT
			Min	Typ	Max	Min	Typ	Max	
V _{NOISE}	Input noise voltage	f _O =30Hz f _O =1kHz		8 5			8 5	12 6	nV/ $\sqrt{\text{Hz}}$ nV/ $\sqrt{\text{Hz}}$
I _{NOISE}	Input noise current	f _O =30Hz f _O =1kHz		2.7 0.7			2.7 0.7		pA/ $\sqrt{\text{Hz}}$ pA/ $\sqrt{\text{Hz}}$
	Channel separation	f=1kHz, R _S =5k Ω		110			110		dB

TYPICAL PERFORMANCE CHARACTERISTICS



SL00334

Figure 3. Typical Performance Characteristics

Internally-compensated dual low noise operational amplifier

NE/SE5532/5532A

TEST CIRCUITS




Figure 4. Test Circuits