

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-.-



© COPYRIGHT - By - TE CONNECTIVITY

ALL RIGHTS RESERVED.


LOC
HBDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	CAHNGE LOGO&ADD LINE IDENTIFICATION ECO-12-001771	21Aug2012	YS.H	BH.Y



PART B



PART B

C:MADE IN CHINA

LOT NO. ©

SEE NOTE 5.




©

0.45

0.3 0.3

14.6 ±0.5

4.1 ±0.3

FIGURE FOR PRINTED CIRCUIT BOARD PROCESSING
(BOTTOM VIEW)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN H.Sasaki

CHK Y.Oikawa

APVD A.Nagai

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

OJE-SH-DM SPEC CUSTOMER DRAWING


SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C= 1461400

SCALE 5:1 SHEET 1 OF 2 REV C2

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -

MATERIAL

FINISH

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

© COPYRIGHT - By - TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

HB

-

P

LTR

DESCRIPTION

DATE

DWN

APVD

-

SEE SHEET 1

-

-

-

ⒸⒶ	OBSOLETE	1461400-6	OJE-SH-148DM, 000	107-79010	48V	OJE-SH-148DM	h
	ACTIVE	1461400-5	OJE-SH-124DM, 000	107-79010	24V	OJE-SH-124DM	g
	ACTIVE	4-1419144-9	OJE-SH-118DM, 000	107-79010	18V	OJE-SH-118DM	f Ⓑ
	ACTIVE	1461400-4	OJE-SH-112DM, 000	107-79010	12V	OJE-SH-112DM	e
ⒸⒶ	OBSOLETE	1461400-3	OJE-SH-109DM, 000	107-79010	9V	OJE-SH-109DM	d
ⒸⒶ	OBSOLETE	1461400-2	OJE-SH-106DM, 000	107-79010	6V	OJE-SH-106DM	c
	ACTIVE	1461400-1	OJE-SH-105DM, 000	107-79010	5V	OJE-SH-105DM	b
ⒸⒶ	OBSOLETE	1461400-7	OJE-SH-103DM, 000	107-79010	3V	OJE-SH-103DM	a
	PART STATUS	PART NO	DESCRIPTION	PACKAGE SPEC.	PART B	PART A	TYPE

RELAY TYPE

ⒸⒷ NOTES:

1.LOT NO. SYSTEM AS FOLLOWING:

WEEK
YEAR

ⒸⒶ 5.ADD LOT NO. SYSTEM AS FOLLOWING;

1	1	A
I	II	III

I, DIGITS FOR DAY OF THE WEEK

1...MONDAY IN THIS WEEK;

2...TUESDAY IN THIS WEEK;

.....

7...SUNDAY IN THIS WEEK

II, DIGITS FOR SHIFT OF THE DAY

1...DAY SHIFT IN THIS DAY;

2...NIGHT SHIFT IN THIS DAY;

III, ONE CHARACTER

DISTINGUISH THE LINE

IDENTITY, SUCH AS:

A,B,.....Z

ⒸⒶ 2.TERMINAL DIMENSION IS BEFORE SOLDER DIP;

ⒸⒶ 3.FOR THE TIN-PLATING OF THE PINS:

+0.1mm FOR WIDTH,THICKENSS AND DIAMETER.

+0.5mm FOR LENGTH.

ⒸⒶ 4.MARKING FROM INK TO LASER.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	H.Sasaki		-
		CHK	Y.Oikawa		-
DIMENSIONS: mm		APVD	A.Nagai		-
		PRODUCT SPEC	-		
		APPLICATION SPEC	-		
		WEIGHT	-		
MATERIAL	FINISH	CUSTOMER DRAWING			
		SCALE	5:1	SHEET	2 OF 2
		REV	C2		

INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM
		UV RESIN	SEEL (VENT HOLE)	16
		EPOXY RESIN	SEEL (BASE & BOBBIN)	15
		3UEW	MAGNETIC WIRE	14
94V-0		P.B.T	CASE	13
94V-0		P.B.T	BASE	12
94V-0		P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	COIL TERMINAL	10
94V-0		P.P.S	CARD	9
		Ag ALLOY	MOVABLE CONTACT	8
		Ag	NO.CONTACT	7
		STEEL	HINGE SPRING	6
	SOLDER DIP	PBP	NO.TERMINAL	5
	SOLDER DIP	PBS	MOVABLE SPRING	4
	NIP	STEEL	CORE	3
	NIP	STEEL	ARMATURE	2
	NIP	STEEL	YOKE	1

TE Connectivity

OJE-SH-DM SPEC CUSTOMER DRAWING

SIZE: A3 CAGE CODE: 00779 DRAWING NO: 1461400 RESTRICTED TO: -