





MATERIAL NUMBER	OLD PART NUMBER	FINISH LENGTH
130013-0409	1R4G06A20A120	1.0'±.75-0 [.3M±19.1-0]

VOLTAGE RATING	600 VAC/VDC
AMPERAGE RATING	10A
PROJECTION	IP67
OPERATING TEMPERATURE	-20° C TO 105° C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E152210
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837



- WIRING DIAGRAM**
- 1 BLACK
 - 2 WHITE
 - 3 RED
 - 4 GREEN-YELLOW

ITEM.	QTY.	COMPONENT	MATERIAL	FINISH
1	1	FLAG LABEL	PLASTIC FILM	BLACK/YELLOW
2	4	CONDUCTOR-16 AWG. 26X#30 COPPER STRANDING 600V	PVC	SEE WIRING DIAGRAM
3	1	RECEPTACLE SHELL	ALUMINUM	ANODIZED
4	4	CONTACT PIN	COPPER ALLOY	GOLD PLATED
5	1	4 POLE INSERT	PVC	YELLOW
6	1	POTTING	EPOXY	BLACK

RELEASED EC NO: WNA2010-0423 DRAWN BY: CHKO.B. WOODMAN CHECKED BY: JFMURPHY APPROVED BY: JFMURPHY DATE: 2010/01/14	QUALITY SYMBOLS =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED) 4 PLACES ± .005 3 PLACES ± .010 2 PLACES ± .015 1 PLACE ± .025 ANGULAR ± 1/2°	DIMENSION STYLE IN/MM	SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	DRAWN BY S. GARCIA DATE 2009/07/02	CHECKED BY B. WOODMAN DATE 2009/07/02	APPROVED BY JFMURPHY DATE 2010/01/14	TITLE MALE FLANGE RECEPTACLE MINI-CHANGE 4P 16AWG PVC	MOLEX INCORPORATED	MATERIAL NO. SEE CHART	DOCUMENT NO. SD-130013-010	SHEET NO. 1 OF 1