






- † Red band indicates fully mated
 †† Blue band indicates rear release contact retention system
 ★ .059 dia min.
 1.5 dia min., 3 lockwire holes formed lockwire hole design (6 holes) is optional

Note: -Drawing not to Scale
 -Dimensions subject to change
 -Dimensions are in Inches, Millimeters (MM) & Blue color
 Property of Amphenol Aerospace.
 All rights reserved.

Part No.:
D38999/24SC35BB

Amphenol[®] Aerospace
 40-60 Delaware Avenue
 Sidney, NY 13838-1395
 800-678-0141
 Cage Code: 77820
www.amphenol-aerospace.com



Amphenol Aerospace
40-60 Delaware Avenue
Sidney, NY 13838-1395
Phone: 800-678-0141 - **Fax:** 607-563-5157
Email: info@amphenol-aerospace.com
Website: www.amphenol-aerospace.com

Matthew Mullins
Product Line Manager
Core Products
Phone: 607-563-5673
Email: mmullins@amphenol-aao.com

Specifications

Connector Type	D38999/
Shell Style	Jam Nut Receptacle
Shell Material	Steel
Shell Finish	Nickel Plated
Insulation Resistance	5000 megohms min. @500 VDC25C
Operating Temperature [Min]	-65°C
Operating Temperature [Max]	+200°C
Shielding Effectiveness	65dB@10GHz
Durability	500 Hour Salt Spray
Contact Type	B
Contact Description	Less Sockets

Contacts

Insert Arrangement	
Shell Size	C
Insert Arrg	35
Service Rating	M
Total # Contacts	22
Test Current	5 AMPS
Wire Size for 22D	28, 26, 24, 22
Contact Size 22D	22
Number of Contacts	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[D38999/24SC35BB](#)