

**MICRO SWITCH**FREEPORT ILLINOIS
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

1HS3**1HS3**

PAGE 1 OF 1

MDRAWING
NUMBERISSUE
17

REPLACES

RELEASE NO.

CHECK

REVISIONS

A	CO17633	M B F	14 FEB 63
B	CO30206	D B W	13 MAR 72
C	CO55162	T S K	27 NOV 85
D	CO62736	M A M	15 MAR 88
E	CO61043	B G S	16 SEP 88
F	CO72580	D A W	20 AUG 92
G	CO75625	J D B	14 JULY 93
H	CO76375	W E S	31 AUG 93
J	CO94122	T S M	12 MAR 99

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK

CHECK


CHECK

CHECK

CHECK

CHECK

CHECK

**NOTE-**

- ⚠ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000±.002 CENTERS
- 2 - TRAVEL CHARACTERISTICS ARE REFERENCED FROM THE UPPER SURFACE OF THE MOUNTING HOLES WITH THIS CONSTRUCTION
- 3 - FOR USE IN AMBIENT TEMPERATURE RANGE FROM MINUS 65° F TO PLUS 250° F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE — — — — 10-22 OZ

RELEASE FORCE — — — — 4 OZ MIN

DIFFERENTIAL TRAVEL — — — .020 MAX

OVERTRAVEL — — — — .010 MIN

ELECTRICAL DATACONTACT ARRANGEMENT
S P D TLINE
VOLTAGEINDUCTIVE
LOADRESISTIVE
LOAD

28 VDC

8 AMP
(SEA LEVEL - 100,000 FT)

25 AMP

125 VAC

1 AMP
(SEA LEVEL - 70,000 FT)

.5 AMP

L 277 1A-125VAC, 5A-28VDC

AL



SCALE FULL —

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES**TOLERANCES ARE:**

ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT 1.6 OZ MAX

FO-50378

FORMTEK

DRAWN

M B F 14 FEB 63