






MATERIALS		SPECIFICATIONS	
BODY: Phenolic, UL94 V-0		FUNCTION: 1P1T OFF-(ON)	
ACTUATOR: Nickel Plated Brass		RATINGS: ANSI/UL1054 and CAN/CSA C22.2 No.55 (E194579): 20A 125VAC [cURus] 15A 277VAC [cURus] 1.5HP 125/277VAC [cURus]	
BUSHING: Nickel Plated Brass		CONTACT RESISTANCE: Initial: 10mΩ Max. Insulation Resistance: 10MΩ Min.	
HOUSING: Nickel Plated Steel		DIELECTRIC STRENGTH: 1,500VAC for 1 Minute	
HARDWARE: Nickel Plated Brass		OPERATING LIFE: 6,000 Cycles [cURus]	
SPACER PLATE: Epoxy Board		TEMPERATURE: Operating: 0°C to 85°C [cURus]	
SPRING: Steel		APPROVALS: ROHS COMPLIANT	
ACTUATOR PLUNGER: Phenolic, UL94 V-0			
MOBILE CONTACT BAR: Silver Plated Copper			
CENTER PIVOT: Silver Plated Copper			
CONTACTS: Silver Alloy Clad Copper			
TERMINALS: Brass			



SUGGESTED PANEL CUTOUT

ALTERNATE PANEL CUTOUT

SCHEMATIC



ACTUATOR	B	10/06/10	CAB
BODY	B	10/06/10	CAB
MATERIALS	B	10/06/09	CAB
SPECIFICATIONS	B	10/06/09	CAB
REFERENCE	REV.	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

A	B
REV.	CORRECTED PANEL CUTOUT, SPECIFICATIONS, AND MATERIALS
	INITIAL RELEASE
	DESCRIPTION
	FOR
	DATE
	DRAWN BY

DIMENSIONS	INCHES [MILLIMETERS]
GENERAL TOLERANCES	±0.008 [±0.2] / ±1°
SCALE	DRAWING NOT TO SCALE
PROJECTION	

TITLE		ST144D00	
DRAWING NUMBER		DATE	
34-ST144D00		JUNE 10, 2010	
		REVISION	
		B	