



PART NO.	ENG. NO.
02-06-8103	1778-P(913)L
02-06-6123	1778-(563)L
02-06-6122	1778-(568)L
02-06-6121	1778-(575)L
02-06-8104	1778-(P913)



LEGEND

1778-(****)*-*

P=PREPLATE
BLANK=POSTPLATE
FINISH CODE





MATERIAL
BLANK=MAT'L. NOTE 1
FORM
L=LOOSE

NOTES:

1. TERMINAL FOR USE WITH (1.57)/.062 SERIES HOUSINGS.
2. THIS PART CONFORMS TO PRODUCT SPEC. 02-06.

FINISH CODES:

- 913 HOT TIN-LEAD DIP (.00254)/.000100 MIN.
- 568 SELECT GOLD PLATE (.00051)/.000020 MIN. IN CONTACT AREA,
SELECT TIN-LEAD (.00508)/.0000200 MIN. IN TAIL AREA,
OVER (.00076)/.000030 MIN. NICKEL OVERALL.
- 575 SELECT GOLD PLATE (.00127)/.000050 MIN. IN CONTACT AREA,
SELECT TIN-LEAD (.00127)/.000050 MIN. IN TAIL AREA,
OVER (.00127)/.000050 MIN. NICKEL OVERALL.
- 563 SELECT GOLD PLATE (.00076)/.000030 MIN. IN CONTACT AREA,
SELECT TIN-LEAD (.00254)/.000100 MIN. IN TAIL AREA,
OVER (.00127)/.000050 MIN. NICKEL OVERALL.



SECT. "A-A"
SCALE:20X

MATERIAL NOTE:

1. CARTRIDGE BRASS, ALLOY #C26000
(.20)/.008 THICK, EXTRA SPRING TEMPER.

DIMENSIONS SHOWN (METRIC) INCH		TITLE	
UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2°		TERMINAL, MALE (1.57)/.062 DIA. P.C. TAIL TYPE	
3 PLACE ± .010	METRIC ---	SHEET NO. 1 OF 1	
2 PLACE ± .014	± 0.25	DATE 12 / 3 / 87	
1 PLACE ---	± 0.36	REV. & REDRAWN PER ECR 10372 SEP 12-3-87 RW	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		REV. & REDRAWN PER ECR 10372 SEP 12-3-87 RW	
DRWG. BY CEP	CHKD. BY RW	PART NO. SD-1778-*	
APP'D. BY RAS	SCALE B ± 1	FILE NAME SD1778X1.DWG	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.		DIV. CP	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[02-06-8104](#)