

Small Signal Zener Diodes

Features

- Silicon Planar Power Zener Diodes.
- Standard Zener voltage tolerance is $\pm 2\%$.

Applications

Voltage stabilization

Mechanical Data


Case: DO-35 Glass case

Weight: approx. 125 mg

Packaging codes/options:

TAP / 10 k per Ammopack (52 mm tape), 30 k/box

TR / 10 k per 13 " reel , 30 k/box



94 9367

Absolute Maximum Ratings

$T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified

Parameter	Test condition	Symbol	Value	Unit
Power dissipation	$T_L \leq 75\text{ }^{\circ}\text{C}$	P_V	500	mW
Z-current		I_Z	P_V/V_Z	mA
Junction temperature		T_j	200	$^{\circ}\text{C}$
Storage temperature range		T_{stg}	- 65 to + 200	$^{\circ}\text{C}$

Thermal Characteristics

$T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified

Parameter	Test condition	Symbol	Value	Unit
Junction ambient	$l = 9.5\text{ mm (3/8 ")}$, $T_L = \text{constant}$	R_{thJA}	300	K/W

Electrical Characteristics

$T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified

Parameter	Test condition	Symbol	Min	Typ.	Max	Unit
Forward voltage	$I_F = 200\text{ mA}$	V_F			1.1	V

1N5221C to 1N5267C



Vishay Semiconductors

Electrical Characteristics

1N5221C...1N5267C

Partnumber	Nominal Zener Voltage ¹⁾	Test Current	Maximum Dynamic Impedance ¹⁾	Maximum Dynamic Impedance	Typical Temperature of Coefficient	Maximum Reverse Leakage Current	
	@ I_{ZT} , V_Z					I_R	V_R
	V	mA	Ω	Ω	α (%/K)	μA	V
1N5221C	2.4	20	30	1200	-0.085	100	1
1N5222C	2.5	20	30	1250	-0.085	100	1
1N5223C	2.7	20	30	1300	-0.080	75	1
1N5224C	2.8	20	30	1400	-0.080	75	1
1N5225C	3	20	29	1600	-0.075	50	1
1N5226C	3.3	20	28	1600	-0.070	25	1
1N5227C	3.6	20	24	1700	-0.065	15	1
1N5228C	3.9	20	23	1900	-0.060	10	1
1N5229C	4.3	20	22	2000	+0.055	5	1
1N5230C	4.7	20	19	1900	+0.030	5	2
1N5231C	5.1	20	17	1600	+0.030	5	2
1N5232C	5.6	20	11	1600	+0.038	5	3
1N5233C	6	20	7	1600	+0.038	5	3.5
1N5234C	6.2	20	7	1000	+0.045	5	4
1N5235C	6.8	20	5	750	+0.050	3	5
1N5236C	7.5	20	6	500	+0.058	3	6
1N5237C	8.2	20	8	500	+0.062	3	6.5
1N5238C	8.7	20	8	600	+0.065	3	6.5
1N5239C	9.1	20	10	600	+0.068	3	7
1N5240C	10	20	17	600	+0.075	3	8
1N5241C	11	20	22	600	+0.076	2	8.4
1N5242C	12	20	30	600	+0.077	1	9.1
1N5243C	13	9.5	13	600	+0.079	0.5	9.9
1N5244C	14	9	15	600	+0.082	0.1	10
1N5245C	15	8.5	16	600	+0.082	0.1	11
1N5246C	16	7.8	17	600	+0.083	0.1	12
1N5247C	17	7.4	19	600	+0.084	0.1	13
1N5248C	18	7	21	600	+0.085	0.1	14
1N5249C	19	6.6	23	600	+0.086	0.1	14
1N5250C	20	6.2	25	600	+0.086	0.1	15
1N5251C	22	5.6	29	600	+0.087	0.1	17
1N5252C	24	5.2	33	600	+0.088	0.1	18
1N5253C	25	5	35	600	+0.089	0.1	19
1N5254C	27	4.6	41	600	+0.090	0.1	21
1N5255C	28	4.5	44	600	+0.091	0.1	21
1N5256C	30	4.2	49	600	+0.091	0.1	23
1N5257C	33	3.8	58	700	+0.092	0.1	25
1N5258C	36	3.4	70	700	+0.093	0.1	27
1N5259C	39	3.2	80	800	+0.094	0.1	30
1N5260C	43	3	93	900	+0.095	0.1	33
1N5261C	47	2.7	105	1000	+0.095	0.1	36
1N5262C	51	2.5	125	1100	+0.096	0.1	39
1N5263C	56	2.2	150	1300	+0.096	0.1	43
1N5264C	60	2.1	170	1400	+0.097	0.1	46

Partnumber	Nominal Zener Voltage ¹⁾	Test Current	Maximum Dynamic Impedance ¹⁾	Maximum Dynamic Impedance	Typical Temperature of Coefficient	Maximum Reverse Leakage Current	
	@ I_{ZT} , V_Z	I_{ZT}	Z_{ZT} @ I_{ZT}	Z_{ZK} @ $I_{ZK} = 0.25 \text{ mA}$	@ I_{ZT}	I_R	V_R
	V	mA	Ω	Ω	α (%/K)	μA	V
1N5265C	62	2	185	1400	+0.097	0.1	47
1N5266C	68	1.8	230	1600	+0.097	0.1	52
1N5267C	75	1.7	270	1700	+0.098	0.1	56

¹⁾ Based on dc-measurement at thermal equilibrium; lead length = 9.5 (3/8 "); thermal resistance of heat sink = 30 K/W

Typical Characteristics ($T_{amb} = 25^\circ\text{C}$ unless otherwise specified)




Figure 1. Thermal Resistance vs. Lead Length




Figure 3. Typical Change of Working Voltage vs. Junction Temperature




Figure 2. Typical Change of Working Voltage under Operating Conditions at $T_{amb}=25^\circ\text{C}$




Figure 4. Total Power Dissipation vs. Ambient Temperature




Figure 5. Temperature Coefficient of V_Z vs. Z-Voltage




Figure 8. Z-Current vs. Z-Voltage




Figure 6. Diode Capacitance vs. Z-Voltage




Figure 9. Z-Current vs. Z-Voltage




Figure 7. Forward Current vs. Forward Voltage




Figure 10. Differential Z-Resistance vs. Z-Voltage





Figure 11. Thermal Response

Package Dimensions in mm (Inches)



Ozone Depleting Substances Policy Statement

It is the policy of Vishay Semiconductor GmbH to

1. Meet all present and future national and international statutory requirements.
2. Regularly and continuously improve the performance of our products, processes, distribution and operating systems with respect to their impact on the health and safety of our employees and the public, as well as their impact on the environment.

It is particular concern to control or eliminate releases of those substances into the atmosphere which are known as ozone depleting substances (ODSs).

The Montreal Protocol (1987) and its London Amendments (1990) intend to severely restrict the use of ODSs and forbid their use within the next ten years. Various national and international initiatives are pressing for an earlier ban on these substances.

Vishay Semiconductor GmbH has been able to use its policy of continuous improvements to eliminate the use of ODSs listed in the following documents.

1. Annex A, B and list of transitional substances of the Montreal Protocol and the London Amendments respectively
2. Class I and II ozone depleting substances in the Clean Air Act Amendments of 1990 by the Environmental Protection Agency (EPA) in the USA
3. Council Decision 88/540/EEC and 91/690/EEC Annex A, B and C (transitional substances) respectively.

Vishay Semiconductor GmbH can certify that our semiconductors are not manufactured with ozone depleting substances and do not contain such substances.

We reserve the right to make changes to improve technical design
and may do so without further notice.

Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer. Should the buyer use Vishay Semiconductors products for any unintended or unauthorized application, the buyer shall indemnify Vishay Semiconductors against all claims, costs, damages, and expenses, arising out of, directly or indirectly, any claim of personal damage, injury or death associated with such unintended or unauthorized use.

Vishay Semiconductor GmbH, P.O.B. 3535, D-74025 Heilbronn, Germany
Telephone: 49 (0)7131 67 2831, Fax number: 49 (0)7131 67 2423



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

<u>1N5227C-TAP</u>	<u>1N5267C-TAP</u>	<u>1N5247C-TAP</u>	<u>1N5237C-TAP</u>	<u>1N5257C-TAP</u>	<u>1N5245C-TAP</u>	<u>1N5265C-TAP</u>
<u>1N5225C-TAP</u>	<u>1N5255C-TAP</u>	<u>1N5235C-TAP</u>	<u>1N5248C-TAP</u>	<u>1N5228C-TAP</u>	<u>1N5258C-TAP</u>	<u>1N5238C-TAP</u>
<u>1N5241C-TAP</u>	<u>1N5221C-TAP</u>	<u>1N5261C-TAP</u>	<u>1N5251C-TAP</u>	<u>1N5231C-TAP</u>	<u>1N5234C-TAP</u>	<u>1N5254C-TAP</u>
<u>1N5244C-TAP</u>	<u>1N5224C-TAP</u>	<u>1N5264C-TAP</u>	<u>1N5253C-TAP</u>	<u>1N5233C-TAP</u>	<u>1N5263C-TAP</u>	<u>1N5223C-TAP</u>
<u>1N5243C-TAP</u>	<u>1N5256C-TAP</u>	<u>1N5236C-TAP</u>	<u>1N5266C-TAP</u>	<u>1N5226C-TAP</u>	<u>1N5246C-TAP</u>	<u>1N5260C-TAP</u>
<u>1N5240C-TAP</u>	<u>1N5230C-TAP</u>	<u>1N5250C-TAP</u>	<u>1N5242C-TAP</u>	<u>1N5222C-TAP</u>	<u>1N5262C-TAP</u>	<u>1N5252C-TAP</u>
<u>1N5232C-TAP</u>	<u>1N5259C-TAP</u>	<u>1N5239C-TAP</u>	<u>1N5229C-TAP</u>	<u>1N5249C-TAP</u>		