




1. FOR USE WITH BOEING BMS13-65 OH & ADAMS RUSSELL FC28Z CABLES

2. FOR CABLING INSTRUCTIONS SEE 3-546-2.

3. FOR CRIMPING USE DIE KTH-2212.

4. INTERFACE PER MIL-STD-348, FIG. 304-1.

5. MARK PACKAGE: KINGS 1206-22-9

YRWBK (DATE CODE)

6. CENTER CC

7. MATERIALS:

INSULATORS: TEFLON, ASTM-D-1710

GASKET: SIL. RUB., A-A-59588

K-GRIP SLEEVE: COM. BRONZE TUBE, ASTM B135

OUTER CONTACT, C-RING: PHOS. BRONZE

CRIMP CONTACT: BER. COP., ASTM-B-

ALL

8. FINISHES:

CON/LACIS: .000050 MIN GOLD PLATE, PER ASM-B-488 OVER .000050 MIN NICKEL PER AMS-DQ-N-290 (KOHs),
OUTED CONTACT .000006 MAX OUTED PER ASTM D 3700 OUTED PER ASTM D 3774 (S US)

CULIER CONIACI : .000200 MIN SILVER PER ASIM-B-700 OVER .000020 MIN COPPER PER ASIM B/34 (KONTS

ALL OTHER METAL PARTS: .000050 MIN NICKEL PER AMS-QQ-N-290 OVER .000050 MIN COPPER PER ASIM B/34 (KOHs),

9. ELECTRICAL CHARACTERISTICS:

NOMINAL IMPEDANCE: 50 OHMS
VOLTAGE RATING: 1000 VDC

VOLTAGE RATING: 1000 VRMS
FREQUENCY RANGE: DC TO 11 GHz

FREQUENCY RANGE: DC TO 11 GHz

10. WEIGHT: 70.2 GRAM

REV/SIONS	
ISSUE	CHANGES
0	ER 35256 JCA 12/16/93
1	CN 35739 A MJB 08/10/94
2	CN 38322 E TML 06/15/01
D	REVISED PER DMF304 & ER34270 CY 09/02/11

CUSTOMER
SALES DRAWING

THIS DRAWING, THE DESIGNS AND IDEAS EMBODIED IN THE DEVICE TO WHICH IT RELATES, AND THE METHOD OF PRODUCING THE DEVICE, ARE THE PROPERTY OF WINCHESTER ELECTRONICS CORPORATION AND SHALL NOT BE EMPLOYED, COPIED, OR DISCLOSED TO ANYONE, IN ANY MANNER WITHOUT THE CONSENT OF WINCHESTER ELECTRONICS CORPORATION.

SCALE 4:1

APPROX SURFACE AREA

WAS: E-17522

CAGE CODE: 91836

REF: BOEING

PLUG, ANGLE, N

DRAWN	JCA	DATE	04/26/93
DESIGN	JT	DATE	04/27/93
APPR.		DATE	

SKINGS®
by WINCHESTER
Winchester Electronics
62 Barnes Industrial
Road North
B
SIZE

1206-22-9