




AX17251 SERIES



External Dimensions



Frame: Aluminum Alloy
Impeller: Plastic (UL: 94V-0)
Motor Structure: Capacitor-Run Induction Motor.
Motor Protection: Thermal Protect.
Lead wire: UL 1015 AWG22
OPERATING TEMP*: $-10^{\circ}\text{C} \sim 70^{\circ}\text{C}$
*: $-10^{\circ}\text{C} \sim 60^{\circ}\text{C}$ for fans with sleeve/ball combination bearings.

Specifications(Nominal)


*: Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: $\odot$ =Ball $\otimes$ =Sleeve $\bigcirc$ =1B1S $\bullet$ =Hypro bearing


Frame size (mm)	Model No.	Bearing System Type	Volt. (VAC)	Freq. (Hz)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM)	Maximum AirFlow (CFM)	Maximum Pressure (InAq)	Maximum Pressure (mmAq)	*Noise Level (dB/A)	Weight (g)
172x150x51	AX17511HB-C	$\odot$	115	50/60	0.36/0.37	40.00/41.40	2850/3300	6.792/7.782	240.0/275.0	0.655/0.727	16.637/18.465	56.0/61.0	970
	AX17512HB-C	$\odot$	230		0.16/0.19	34.50/42.00							

Specifications subject to change without notice.

50Hz



60Hz



*Safety approvals
115V

✓	✓			

230V

✓	✓		✓	✓