


max. 13,5 m³/h

DC axial fans

Series 400 40 x 40 x 20 mm



Highlights:

- Compact fan with low power consumption.
- Some models suitable for use at high ambient temperatures.

General characteristics:

- Material: fibreglass-reinforced plastic. Impeller PA, housing PBT.
- Fully integrated electronic commutation.
- Protected against reverse polarity and locking.
- Connection via single strands AWG 28, TR 64. Bared and tin-plated.
- Air exhaust over struts. Direction of rotation counter-clockwise, seen on rotor.
- Mass: 27 g.

Nominal data		Air flow	Air flow	Nominal voltage	Voltage range	Sound pressure level	Sound power level	Sinter sleeve bearings Ball bearings	Power input	Nominal speed	Temperature range	Service life L ₁₀ (20 °C) ebm-papst Standard	Service life (60 °C) ebm-papst Standard	Life expectancy L ₁₀ Δ (40 °C) see P. 15	Curve	Specials
Type		m³/h	CFM	VDC	VDC	dB(A)	Bel(A)	■ / ■	Watts	RPM	°C	Hours	Hours	Hours	P. 110/118	
405		10,0	5,9	5	4,5...5,5	18	3,8	■	0,9	6 000	-20...+70	50 000 / 20 000	62 500	1	/2	
412		10,0	5,9	12	10...14	18	3,8	■	0,9	6 000	-20...+70	50 000 / 20 000	62 500	1	/2	
412 H		13,5	7,9	12	10...14	29	4,7	■	1,6	8 100	-20...+60	45 000 / 15 000	47 500	2	/39	
414		10,0	5,9	24	20...28	18	3,8	■	1,0	6 000	-20...+70	50 000 / 20 000	62 500	1	/2	
414 H		13,5	7,9	24	20...26,5	29	4,7	■	1,6	8 100	-20...+60	45 000 / 15 000	47 500	2	/2	
Model with temperature range up to +85 °C.																
412-099		10,0	5,9	12	10...14	18	3,8	■	0,8	6 000	-20...+85	50 000 / 20 000	62 500	1		

