



## Product: [GUXWA12](#)

Indoor/Outdoor Distribution Steel Wire Armour 12 Fibers G657A1-OS2

### Product Description

Universal (Indoor/Outdoor) Steel Wire Armour Mini Breakout Rodent Protection Tight Optical Cable 12 x 9/125-G657A1-OS2 A/I-VQ(ZN)H(SR)H

### Technical Specifications

Construction Type:	Distribution
--------------------	--------------

### Product Overview

Environmental Space:	Indoor/Outdoor - Euroclass B2ca
Suitable Applications:	For outdoor and indoor use in structured (data) wiring systems such as industrial backbone, campus backbone, building backbone (riser) and/or horizontal cabling. For outdoor and indoor use in networks for industrial, telecom, cable TV and/or broadcast. Support all computer network applications such as FDDI, Gigabit Ethernet and ATM.

### Construction

#### Fiber Cable Construction

Fiber Type	Fiber Grade acc. ITU-T	Fiber Count
OS2	G657A1	12

Fiber Color Coding: TIA coding (Gxxxxx.T): Blue, Orange, Green, Brown, Gray, White, Red, Black, Yellow, Violet, Pink, Aqua.

Fiber Color Coding 2: Europe coding (Gxxxxx.0): Red, Natural, Yellow, Blue, Green, Violet, Brown, Black, Orange, Aqua, Pink, White.

#### Buffer Specification

Fiber Type	Buffer Construction	Buffer Material	Buffer Diameter
OS2	Tight	LSZH - Low Smoke Zero Halogen	0.9 mm

Cable Core Water Tight: Yes

Cable Core Water Blocking: Waterblocking Glass Yarns

Bulk Cable Weight: 332 kg/km

### Jacket Specifications

Number of Jackets:	Double Jacket
Type of Armor:	Steel Wire
Material:	LSZH - Low Smoke Zero Halogen

#### Outer Jacket Material

Material	Nominal Diameter	Ripcord
LSZH - Low Smoke Zero Halogen	14.0 mm	1

### Optical Characteristics

Fiber Core Diameter:	9 µm
Max Attenuation at 1310 nm:	0.50 dB/km
Max Attenuation at 1550 nm:	0.30 dB/km

### Mechanical Characteristics

#### Mechanical Tests

Description	Tested Standard	Requirement/Value	According to Family Specification
-------------	-----------------	-------------------	-----------------------------------

Cable Min. Bend Radius Installation (Short Term)	IEC 60794-1-21-E6	268 mm	IEC 60794-2-20
Cable Min. Bend Radius Operation (Long Term)	IEC 60794-1-21-E11	201 mm	IEC 60794-2-20
Cable Max. Tensile Strength Operation (Long Term)	IEC 60794-1-21-E1	3230 N (726 lbf)	IEC 60794-2-20
Cable Max. Crush Resistance Installation (Short Term)	IEC 60794-1-21-E3	20 kN/m	IEC 60794-2-20
Cable Max. Crush Resistance Operation (Long Term)	IEC 60794-1-21-E3	18 kN/m	IEC 60794-2-20

## Temperature Range

Operating Temp Range:	-30 °C to +70 °C
Installation Temp Range:	-5 °C to +50 °C
Storage Temp Range:	-30 °C to +70 °C

## Standards

UL Rating/Flame Test:	Non-UL Rated
IEC Flammability:	IEC 60332-1-2
Reaction to Fire - Bundle Flame Test:	IEC 60332-3-22
CPR Euroclass:	B2ca-s1,d1,a1
REACH:	Compliant
IEC Compliance:	IEC 60794
EU Directive 2011/65/EU (ROHS II):	Compliant
UV/ Sunlight Protection:	yes

## History

### Variants

Item #	Color	Length
GUXWA12.012100	Black	2,100 m

Update and Revision: Revision Number: 0.78 Revision Date: 07-03-2020

© 2020 Belden, Inc.

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.