


SULLINS ELECTRONICS CORP

SAN MARCOS, CA 760-744-0125 FAX 760-744-6081



HAIRPIN BELLOWS CONTACTS

$$E = 3.335 \pm .020 \quad [84.71 \pm 0.51]$$




$$D = 3.075 \pm .010 \quad [78.11 \pm 0.25]$$

$$C = 2.760 \pm .015 \quad [70.10 \pm 0.38]$$

$$B = 2.600 \pm .008 \quad [66.04 \pm 0.20]$$

$$A = 2.400 \pm .008 \quad [60.96 \pm 0.20]$$

$$W = 0.370 \quad [9.40]$$



bsp MARKING:

bsp 3 ... 47 49

bsp 4 ... 48 50

bsp

bsp

$$F = 2.650 \pm .015 \quad [67.31 \pm 0.38]$$

- 1.0 SPECIFICATIONS FOR A DUAL 25/50 POSITION EDGE CARD CONNECTOR
- 2.0 INSULATION MATERIAL: THERMOPLASTIC POLYESTER
- 3.0 CONTACT MATERIAL: CA510 PHOSPHOR BRONZE GRADE C
- 4.0 TEMPERATURE: TO 125 DEGREES C CONTINUOUS
- 5.0 PLATING: .000010" GOLD ON CONTACT SURFACE, .000100" TIN ON TAILS, .000050" NICKEL UNDERPLATE
- 6.0 VOLTAGE RATING: 600 VDC MINIMUM AT SEA LEVEL
- 7.0 UL FLAMMABILITY RATING: 94V-0
- 8.0 CURRENT RATING: 3 AMPERES
- 9.0 VOLTAGE DROP: 30 MILLIVOLTS AT RATED CURRENT
- 10.0 INSULATION RESISTANCE: 5,000 MEGA OHMS
- 11.0 IDENTIFICATION: PART TO BE MARKED WITH PART NUMBER AND DATE CODE
- 12.0 BOARD THICKNESS ACCOMMODATED: .054 INCH TO .070 INCH
- 13.0 INSERTION FORCE: 16 OZ MAX PER CONTACT PAIR USING .062 INCH BLADE
- 14.0 WITHDRAWAL FORCE: 1 OZ MIN PER CONTACT PAIR USING .054 INCH BLADE
- 15.0 SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
- 16.0 TOLERANCE: $\pm .010$ INCH UNLESS OTHERWISE NOTED
- 17.0 NOT DRAWN TO SCALE

SULLINS PART NUMBER: EZC25DCWH**DATE: 3-9-04**[Print PDF](#)