

Radial Leaded Epoxy Dipped

Technical drawing of a chair showing front and side views with dimensions:

- Front View Dimensions:**
 - L max.**: Maximum length of the seat.
 - H max.**: Maximum height of the backrest.
 - .08 max.**: Maximum thickness of the backrest.
 - .2 ± .04**: Dimension for the seat thickness.
 - L.S. ± .04**: Dimension for the seat length.
- Side View Dimensions:**
 - T max.**: Maximum thickness of the backrest.
 - d**: Diameter of the seat base.

STK
ELECTRONICS
Film Capacitors

L =	.31/8	.41/10.5	.52/13	.73/18.5
	↓	↓	↓	↓
L.S	.20/5.0	.28/7.5	.39/10	.6/15
d =	.020/5	.024/6	.024/6	.032/8

* Lead forming available

μF	63VDC		
	T	H	L
.0001	18/4.5	30/7.5	31/8
.00012	18/4.5	30/7.5	31/8
.00015	18/4.5	30/7.5	31/8
.00018	18/4.5	30/7.5	31/8
.00022	18/4.5	30/7.5	31/8
.00027	18/4.5	30/7.5	31/8
.00033	18/4.5	30/7.5	31/8
.00039	18/4.5	30/7.5	31/8
.00047	18/4.5	30/7.5	31/8
.00056	18/4.5	30/7.5	31/8
.00068	18/4.5	30/7.5	31/8
.00082	18/4.5	30/7.5	31/8
.001	18/4.5	30/7.5	31/8
.0012	18/4.5	30/7.5	31/8
.0015	18/4.5	30/7.5	31/8
.0018	18/4.5	30/7.5	31/8
.0022	18/4.5	30/7.5	31/8
.0027	18/4.5	30/7.5	31/8
.0033	18/4.5	30/7.5	31/8
.0039	18/4.5	30/7.5	31/8
.0047	18/4.5	31/8	31/8
.0056	18/4.5	31/8	31/8
.0068	18/4.5	31/8	31/8
.0082	18/4.5	31/8	41/10.5
.01	18/4.5	31/8	41/10.5
.012	18/4.5	31/8	41/10.5
.015	18/4.5	31/8	41/10.5
.018	20/5	35/9	41/10.5
.022	22/5.5	39/10	41/10.5
.027	24/6	43/11	41/10.5
.033	26/6.5	45/11.5	41/10.5
.039	22/5.5	43/11	52/13
.047	24/6	47/12	52/13
.056	26/6.5	52/13	52/13
.068	28/7	55/14	52/13
.082	24/6	47/12	73/18.5
.1	26/6.5	49/12.5	73/18.5
.12	28/7	52/13	73/18.5
.15	31/8	55/14	73/18.5
.18	33/8.5	61/15.5	73/18.5
.22	35/9	65/16.5	73/18.5
.27	47/9.5	71/18	73/18.5
.33	41/10.5	79/20	73/18.5
.39	45/11.5	87/22	73/18.5
.47	49/12.5	94/24	73/18.5

Series *Capacitance Tolerance Voltage

F = 1%, G = 2%, H = 2.5%, J = 5%, K = 10%, M = 20%