

# SMD LVPECL SO

## 7.0 x 5.0 x 1.6 mm

### BS Series



#### Features


- SAW base solution.
- 3.3V and 2.5V operation available.
- LVPECL output, output frequencies 150 MHz to 700 MHz.
- Excellent low phase noise and jitter.
- Tri-State function available.
- Applications : Fibre Channel, Gigabit Ethernet, Serial ATA, Serial Attached SCSI, PCI-Express, SDH / SONET.
- RoHS Compliant / Pb Free.

#### Electrical Specifications

| Item / Type                                    | BS                                   |
|------------------------------------------------|--------------------------------------|
| Output Type                                    | LVPECL                               |
| Output Load                                    | 50 $\Omega$ to VDD - 2 V             |
| Oscillation Mode                               | Fundamental                          |
| Supply Voltage                                 | 2.5 V , 3.3 V                        |
| Frequency Range                                | 150 ~ 700 MHz                        |
| Overall Frequency Stability *                  | $\pm 100$ ppm , or specify           |
| Operating Temperature Range                    | -10 ~ + 70 $^{\circ}$ C , or specify |
| Storage Temperature Range                      | - 55 ~ + 125 $^{\circ}$ C            |
| Voltage Vol ( Max. ) / Voh ( Min. )            | VDD - 1.62 V / VDD - 1.025 V         |
| Rise ( Tr ) / Fall ( Tf ) Time ( 20 % ~ 80 % ) | 1 ns Max.                            |
| Supply Current                                 | 80 mA Max.                           |
| Symmetry                                       | 45 ~ 55 %                            |
| Start-up Time                                  | 10 ms Max.                           |
| Phase Jitter ( 12 KHz ~ 20 MHz )               | 1 ps Max.                            |

\* Inclusive of frequency tolerance at 25  $^{\circ}$ C, variation over temperature, supply voltage variation, aging and vibration.


#### Dimensions



#### PAD FUNCTION:

- 1: ENABLE CONTROL or NC
- 2: ENABLE CONTROL or NC
- 3: GND
- 4: OUT
- 5: OUTN
- 6: VDD

\* :External high frequency power supply decoupling required.



Units: mm