








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
C		REVISED PER ECR-21-100678	08APR2021	SS	VS
D		REVISED PER ECR-23-219171	29JUN2023	MC	DS
E		REVISED PER ECR-22-156333	27JUL2023	SKR	MC



RECOMMENDED PANEL OPENING DEMENSIONS
FOR CAP HOUSING 2*6 AND 2*5 AND 2*4 POSITIONS
(TOLERANCE: ±0.15mm)

RECOMMENDED PANEL OPENING DEMENSIONS
FOR CAP HOUSING 2*3 POSITION
(TOLERANCE: ±0.15mm)



- MATERIAL:
LEVEL A: PA66 GLASS FILLED, COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30 (GWT),UL 94V-0
LEVEL B: PBT GLASS FILLED, HOT WIRE IGNITION (HWI) VERSION ARE MOLDED IN A RESIN THAT COMPLIES WITH TE PENDING HOT WIRE IGNITION TEST AND ARE RECOMMENDED FOR USE WITH HWI HOUSINGS THAT ALSO COMPLY, UL 94V-0

2 MATERIAL MARK:
LEVEL A:GWT,LEVEL B:HWI



- APPLICABLE CONTACT P/N
TAB CONTACT:1971238/1971780/82/84/86/88-*,2238067-*,*-2324732-*

- MATING CONN, P/N
PLUG HSG: *-2232266-*,
TPA (LOCK PLATE): *-1971778-*



- RECOMMENDED PANEL THICKNESS:1.0~2.0mm

POS	A	B	C	D	E
2*6	39.70	45.5	37.30	42.70	37.80
2*5	33.70	39.5	31.30	36.70	31.80
2*4	27.70	33.5	25.30	30.70	25.80
2*3	21.70	27.5	19.30		



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TOMMY.WU 26MAR2013	TE Connectivity	
		CHK HAPYE.WU 26MAR2013		
DIMENSIONS:		APVD YUZHONG.MAO 26MAR2013	NAME CAP HOUSING,PANEL MOUNT,DOUBLE ROW POWER TRIPLE LOCK	
mm		PRODUCT SPEC		
		108-106118	SIZE CAGE CODE DRAWING NO	
		APPLICATION SPEC		
		114-106118	RESTRICTED TO	
		WEIGHT		
MATERIAL		Customer Drawing	SCALE 4:1 SHEET 1 OF 2 REV E	




2*5 POSITIONS




2*4 POSITIONS




2*3 POSITIONS





KEYING FOR 2*5 POS.




KEYING FOR 2*4 POS.



KEYING FOR 2*3 POS.



2*6 POSITIONS



KEYING FOR 2*6 POS.

2*6	LEVEL A	DARK GREY	KEY A	5-2232264-6
		BROWN	KEY B	6-2232264-6
		GREEN	KEY C	7-2232264-6
		ORANGE	KEY D	8-2232264-6
2*5	LEVEL A	DARK GREY	KEY A	5-2232264-5
		BROWN	KEY B	6-2232264-5
		GREEN	KEY C	7-2232264-5
		ORANGE	KEY D	8-2232264-5
2*4	LEVEL A	DARK GREY	KEY A	5-2232264-4
		BROWN	KEY B	6-2232264-4
		GREEN	KEY C	7-2232264-4
		ORANGE	KEY D	8-2232264-4
2*3	LEVEL A	BLACK	KEY A	1-2232264-4
		DARK GREY	KEY A	5-2232264-3
		BROWN	KEY B	6-2232264-3
		GREEN	KEY C	7-2232264-3
POS.	MATERIAL	BLACK	KEY A	1-2232264-1
		COLOR	KEY	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

OWN

26MAR2013

TOMMY_WU

CHK

26MAR2013

HAPYE_WU

APVD

26MAR2013

YUZHONG_MAO

DIMENSIONS:

mm

0 PLC

±

1 PLC

±0.35

2 PLC

±0.25

3 PLC

±

4 PLC

±

ANGLES

±

FINISH

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

108-106118

APPLICATION SPEC

114-106118

WEIGHT

MATERIAL

-

Customer Drawing

NAME

CAP HOUSING,PANEL MOUNT,DOUBLE ROW POWER TRIPLE LOCK

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A100779

2232264

-

-

SCALE

SHEET

2

OF

2

REV

E

TE Connectivity