

1

2

3

4

A

B

C


D

A


B

C

D



PC board drilling dimensions(after plating)  
(thickness ≤ 3.20±0.30mm)



## TIN LEAD PART NUMBER

| SHELL | A±0.38 | B±0.12 | C±0.10 | D±0.25 | E±0.07 | PART NUMBER  | PART NUMBER  |
|-------|--------|--------|--------|--------|--------|--------------|--------------|
| 09    | 30.81  | 24.99  | 16.96  | 16.79  | 10.96  | D09P91C4GV00 | D09P91C6GV00 |
| 15    | 39.14  | 33.32  | 25.18  | 25.12  | 19.18  | D15P91C4GV00 | D15P91C6GV00 |
| 25    | 53.03  | 47.04  | 39.12  | 38.84  | 33.12  | D25P91C4GV00 | D25P91C6GV00 |
| 37    | 69.32  | 63.50  | 55.68  | 55.30  | 49.68  | D37P91C4GV00 | D37P91C6GV00 |
|       |        |        |        |        |        | 200 Matings  | 500 Matings  |

## LEAD FREE PART NUMBER

| SHELL | A±0.38 | B±0.12 | C±0.10 | D±0.25 | E±0.07 | PART NUMBER    | PART NUMBER    |
|-------|--------|--------|--------|--------|--------|----------------|----------------|
| 09    | 30.81  | 24.99  | 16.96  | 16.79  | 10.96  | D09P91C4GV00LF | D09P91C6GV00LF |
| 15    | 39.14  | 33.32  | 25.18  | 25.12  | 19.18  | D15P91C4GV00LF | D15P91C6GV00LF |
| 25    | 53.03  | 47.04  | 39.12  | 38.84  | 33.12  | D25P91C4GV00LF | D25P91C6GV00LF |
| 37    | 69.32  | 63.50  | 55.68  | 55.30  | 49.68  | D37P91C4GV00LF | D37P91C6GV00LF |
|       |        |        |        |        |        | 200 Matings    | 500 Matings    |

## GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

European Views

|                                                                                       |               |            |                                                              |        |                                   |          |                                                                                                     |              |                                                                                             |           |  |
|---------------------------------------------------------------------------------------|---------------|------------|--------------------------------------------------------------|--------|-----------------------------------|----------|-----------------------------------------------------------------------------------------------------|--------------|---------------------------------------------------------------------------------------------|-----------|--|
| www.fciconnect.com                                                                    |               |            | surface<br>ISO 1302                                          |        | tolerance std<br>ISO 406 ISO 1101 |          | projection<br> |              | mm<br> |           |  |
|                                                                                       |               |            | TOLERANCES UNLESS OTHERWISE SPECIFIED                        |        |                                   |          |                                                                                                     |              |                                                                                             |           |  |
| Dr                                                                                    | PESSON        | 1995/08/25 | ANGULAR                                                      | LINEAR | 0.X                               | ±0.1     | size<br>A3                                                                                          | Scale<br>2   |                                                                                             |           |  |
| Eng                                                                                   | PESSON        | 1995/08/25 |                                                              |        | 0.XX                              | ±0.1     |                                                                                                     |              |                                                                                             |           |  |
| Chr                                                                                   | NIRMAL GEORGE | 2010/12/11 |                                                              |        | 0.XXX                             | ±0.1     |                                                                                                     |              |                                                                                             |           |  |
| Appr                                                                                  | SUDHIR VARMA  | 2010/12/11 | Product family                                               |        |                                   | D-SUB    | Spec ref -                                                                                          |              |                                                                                             |           |  |
|  |               |            | title<br>MALE DELTA D CONNECTOR EUROPE<br>straight press fit |        |                                   |          | dwg no<br>C01-8646-0360                                                                             |              |                                                                                             | Rev.<br>F |  |
| catalog no                                                                            |               |            | -                                                            |        |                                   | CUSTOMER |                                                                                                     | sheet 1 of 1 |                                                                                             |           |  |

| rev | ecn no    | dr  | date       |
|-----|-----------|-----|------------|
| B   | -         | PES | 1996/07/24 |
| C   | LS05-004  | MPE | 2005/02/10 |
| D   | LS06-0097 | LGO | 2006/07/29 |
| E   | LS06-0186 | LGO | 2006/07/29 |
| F   | I11-0062  | RPK | 2011/04/05 |
| -   | -         | -   | -          |
| -   | -         | -   | -          |

REV F - 2006-04-17

1

2

3

4

PDM: Rev:F

STATUS: Released

Printed: Oct 11, 2011



Copyright FCI.