



Search Results

Evaluate

- FAQ's
- Performance Data
- PDF-TX7000 Shiel ..
- PDF-ETL Channel ..
- PDF-TX7000 Shiel ..
- PDF-TX7000 Shiel ..
- Technology Briefs
- PDF-Marine Coppe ..
- Videos
- WMV-TX7000 Shiel ..

Design a Solution

- Catalog Cut Sheet
- PDF-PSM7004BU-KD
- Specification Sheets
- PDF-TX7000 Shiel ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Installation Instructions
- PDF-TX7000 Shiel ..
- PDF-TX7000 Marin ..
- PDF-TX7000 Shiel ..
- PDF-TX7000 Shiel ..
- PDF-TX7000 Shiel ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'PSM7004BU-KM'

Your search criteria matched only one product, shown below

PSM7004BU-KM



- Exceeds requirements of ISO 11801 Class EA and ANSI/TIA-568-C.2 Category 6A channel standards
- Meets or exceeds the requirements of IEC 61156-5 Category 7 component standards at swept frequencies up to 1000 MHz
- Meets requirements of IEEE 802.3af and IEEE 802.3at for PoE applications
- Robust cable jacket oil and fuel resistant for harsh environments
- Flame rated to meet IEC 60754-1, IEC 60754-2, IEC 61034-2, IEC 60332-3-24
- Chemical resistance tested to mineral oil I RM 902 (IEC 60811-2-1) and diesel fuel I RM 903 (IEC 60811-2-1)
- Third party tested to exceed the application requirements of Det Norske Veritas, American Bureau of Shipping, and ETL
- DNV certification number E-10447
- ABS certification number 10-HS638424-1-PDA
- Ideal for harsh environments encountered in marine applications, including ship and offshore/onshore units

- Cable diameter 8.2 mm (0.322 in) nominal
- Installation temperature range: -15°C to 50°C (5°F to 122°F)
- Operating temperature range: -40°C to 85°C (-40°F to 185°F)
- Descending cable length markings enable easy identification of remaining cable which reduces installation time and cable scrap
- Packaged on a reel

Contact customer service for region availability

▪ Part Number	PSM7004BU-KM
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Category 7 low smoke, halogen free, fire retardant (LSHF-FR), 4-pair S/FTP shielded marine copper cable. Stranded copper conductors are 4 x 2/0.27mm ² . Conductors are twisted in pairs, each individual twisted pair is surrounded by a foil, covered with an overall braided shield and is protected by an oil and fuel resistant, low smoke, halogen free, and fire retardant jacket.
▪ Product Type	Copper Cable
▪ Color	Blue
▪ Cable Color	Blue
▪ Cable Type	S/FTP
▪ Flammability Rating	LSHF-FR
▪ Performance Level	Category 7/Class F
▪ Pricing Description	Copper Cable, Cat 7, 4-Pair, 23 AWG stranded, S/FeetP, LSFR0H SHF1, Std Pallet, 1000m reel
▪ Min. Order UOM	FT
▪ Min. Order Qty.	13120
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.