

1 GHz and 500 MHz High Voltage Differential Probes

TDP1000, TDP0500, P6251 Datasheet



The TDP1000, TDP0500, and P6251 High-voltage Differential Probes provide excellent high-speed electrical and mechanical performance required for today's Switch Mode Power Supply (SMPS), CAN/LIN Bus, and high-speed digital system designs.

Key performance specifications

- 1 GHz and 500 MHz probe bandwidth
- <1 pF differential input capacitance
- 1 M Ω differential input resistance
- ± 42 V (DC + pk AC) differential input voltage
- >18 dB CMRR (at 250 MHz 50X attenuation)

Key features

- Outstanding electrical performance
 - Selectable bandwidth-limiting filters
 - DC reject
- Versatile DUT connectivity
 - Small compact probe head for probing small geometry circuit elements
 - Straight pin, square pin, solder down, variable pitch standard accessories
 - Robust design for reliability
- Easy to use
 - Provides automatic units scaling and readout on the oscilloscope display
 - TDP1000, TDP0500
 - Connect directly to oscilloscopes with the TekVPI™ probe interface
 - Easy access to scope-displayed probe menu for probe setup control and operating status information
 - Remote GPIB/USB probe control through the oscilloscope
 - AutoZero – zeros out output offset
 - P6251
 - Connect directly to the TekProbe™ interface oscilloscopes, or to TekConnect® oscilloscopes using TCA-BNC adapter

Applications

- High-speed switch mode power supply design
- CAN/LIN bus design
- Digital design and characterization
- Manufacturing engineering test
- Research and development

High-voltage differential probes

The TDP1000, TDP0500, and P6251 High-voltage Differential Probes are specifically designed for use with and direct connection to Tektronix oscilloscopes with either the TekVPI™ probe interface, or TekProbe BNC

Interface. These probes achieve high-speed signal acquisition and measurement fidelity by solving three traditional measurement challenges:

- Outstanding Electrical Performance
- Versatile Device-Under-Test Connectivity
- Ease of Use

Specifications

All specifications apply to all models unless noted otherwise.

Warranted characteristics

Bandwidth (probe only)	
TDP1000, P6251	1 GHz
TDP0500	500 MHz
Attenuation	5X, 50X
Differential mode input voltage	±42 v (DC + pk AC); 30 V _{RMS}
Rise time (probe only)	
TDP1000, P6251	≤350 ps
TDP0500	<700 ps
CMRR	>55 dB at 30 kHz
	>50 dB at 1 MHz
	>18 dB at 250 MHz (warranted at 50X attenuation)
Max input voltage (nondestruct)	±100 v (DC + pk AC)
Gain accuracy at DC	±2%

Typical characteristics

Differential input capacitance	<1 pF
Differential input resistance	1 MΩ
Sensitivity/noise level	
5X attenuation	2 mV _{RMS}
	10 mV _{RMS} (referred to the probe output)
50X attenuation	1 mV _{RMS}
	50 mV _{RMS} (referred to the probe output)
Propogation delay	6.5 ns
Common mode input voltage	±35 v (DC + pk AC); 25 V _{RMS}
Differential input offset range	
TDP1000, TDP0500	±42 v (5X or 50X attenuation)
P6251	±4.25 v (5X attenuation)
	±42 v (50X attenuation)

TDP1000, TDP0500, and P6251 1 GHz and 500 MHz High Voltage Differential Probes

DC reject

5X attenuation	0.4 Hz
50X attenuation	4 Hz

Nominal characteristics

Selectable bandwidth filter limits

TDP1000, TDP0500	100 Hz, 10 kHz, 1 MHz, Full
P6251	5 MHz, Full

Oscilloscope interface recommendations

TDP1000, TDP0500	TekVPI™ Probe
P6251	TekProbe BNC Level II
	TekConnect® (TCA-BNC required)

Power requirements

TDP1000, TDP0500 Powered directly by oscilloscopes with the TekVPI interface

P6251 Powered directly by the TekProbe-BNC interface, eliminating the need for additional power supplies and cables when used with TekProbe-BNC oscilloscopes.

May also be powered through the 1103 TEKPROBE power supply for use with non-TekProbe interface instrumentation.

Physical characteristics

Compensation box dimensions

Dimension	TDP1000, TDP0500		P6251	
	in	cm	in	cm
Height	1.6	4.1	1.0	2.6
Width	1.2	3.05	1.6	4.1
Length	4.2	10.7	3.2	8.13
Cable length	47.2 (inches), 1.2 (meters)			

Weight

TDP1000, TDP0500		P6251	
lb	kg	lb	kg
0.320	0.146	0.360	0.163

Ordering information

Models

TDP1000	1 GHz high-voltage differential probe with TekVPI interface.
TDP0500	500 MHz high-voltage differential probe with TekVPI interface.
P6251	1 GHz High-voltage Differential Probe with TekProbe-BNC Level II Interface.

Options

Language options

Opt. L5	Japanese manual
Opt. L7	Simplified Chinese manual

Service options

Opt. C3	Calibration Service 3 Years
Opt. C5	Calibration Service 5 Years
Opt. R3	Repair Service 3 Years (including warranty)
Opt. R5	Repair Service 5 Years (including warranty)
Opt. SILV600	Standard warranty extended to 5 years
Opt. SILV900	Standard warranty extended to 5 years

Additional service products for the TDP0500 or TDP1000

The following are available during either warranty (DW) or postwarranty (PW).

TDP0500-CA1 / TDP1000-CA	A single calibration event or coverage for the designated calibration interval, whichever comes first
TDP0500-R1PW / TDP1000-R1PW	Repair service coverage, 1-year post warranty
TDP0500-R2PW / TDP1000-R2PW	Repair service coverage, 2-year post warranty
TDP0500-R3DW / TDP1000-R3DW	Repair service coverage 3 years (includes product warranty period) 3-year period starts at time of customer instrument purchase
TDP0500-R5DW / TDP1000-R5DW	Repair service coverage 5 years (includes product warranty period) 5-year period starts at time of customer instrument purchase

Additional service products for the P6251

The following are available during either warranty (DW) or postwarranty (PW).

P6251-CA1	A single calibration event or coverage for the designated calibration interval, whichever comes first
P6251-R1PW	Repair service coverage, 1-year post warranty
P6251-R2PW	Repair service coverage, 2-year post warranty
P6251-R3DW	Repair service coverage 3 years (includes product warranty period) 3-year period starts at time of customer instrument purchase
P6251-R5DW	Repair service coverage 5 years (includes product warranty period) 5-year period starts at time of customer instrument purchase

Accessories

Common standard accessories

Description	Quantity included with product	Reorder part number (qty in reorder)
Y-lead set	2 each	196-3434-xx (1)
Solder-down lead set, 1 inch	1 each	196-3504-xx (1)
Solder-down lead set, 3 inch	1 each	196-3505-xx (1)
Micro CKT test tip	3 each	206-0569-xx (1)
Tip savers	2 each	016-1781-xx (2)
Longhorn adapters	2 each	016-1780-xx (5)
Straight-pin probe tips	8 each	016-1891-xx (8)
3-inch ground leads	2 each	196-3437-xx (2)
Color-coding bands	2 each of 5 colors	016-1315-xx (2 each of 5 colors)
Nylon carrying case	1 each	016-1952-xx (1)
CD with technical reference manual and quick start users guides	1 each	063-4110-xx (1)

Standard accessories for the TDP0500 and TDP1000

Description	Qty included with product	Reorder part number (qty in reorder)
Quick start users guide	1 each	
English		071-1974-xx (1)
Japanese (with option L5)		071-1975-xx (1)
Simplified Chinese (with option L7)		071-1976-xx (1)
Documentation Kit CD, Includes: Quick Start Users Guide (English, Japanese, and Simplified Chinese versions); Technical Reference Manual	1 each	063-3941-xx (1)

Standard accessories for the P6251

Description	Qty included with product	Reorder part number (qty in reorder)
Documentation Kit CD, Includes: Quick Start Users Guide (English, Japanese, and Simplified Chinese versions); Technical Reference Manual	1 each	063-4110-xx (1)

Standard warranty

1 year parts and labor.

Recommended accessories

Description	Part number	Quantity
BNC to probe tip adapter	067-1734-xx	1 each
Spring loaded grounds	016-1782-xx	1 package of 6
Twin foot adapter	016-1785-xx	1 package of 4
Twin tip adapter	016-1786-xx	1 package of 4
IC micro grabber	SMK4	1 package of 4
TEKPROBE probe power supply	1103	1 each



Tektronix is registered to ISO 9001 and ISO 14001 by SRI Quality System Registrar.



Product(s) complies with IEEE Standard 488.1-1987, RS-232-C, and with Tektronix Standard Codes and Formats.

ASEAN / Australasia (65) 6356 3900
Belgium 00800 2255 4835*
Central East Europe and the Baltics +41 52 675 3777
Finland +41 52 675 3777
Hong Kong 400 820 5835
Japan 81 (3) 6714 3010
Middle East, Asia, and North Africa +41 52 675 3777
People's Republic of China 400 820 5835
Republic of Korea 001 800 8255 2835
Spain 00800 2255 4835*
Taiwan 886 (2) 2722 9622

Austria 00800 2255 4835*
Brazil +55 (11) 3759 7627
Central Europe & Greece +41 52 675 3777
France 00800 2255 4835*
India 000 800 650 1835
Luxembourg +41 52 675 3777
The Netherlands 00800 2255 4835*
Poland +41 52 675 3777
Russia & CIS +7 (495) 6647564
Sweden 00800 2255 4835*
United Kingdom & Ireland 00800 2255 4835*

Balkans, Israel, South Africa and other ISE Countries +41 52 675 3777
Canada 1 800 833 9200
Denmark +45 80 88 1401
Germany 00800 2255 4835*
Italy 00800 2255 4835*
Mexico, Central/South America & Caribbean 52 (55) 56 04 50 90
Norway 800 16098
Portugal 80 08 12370
South Africa +41 52 675 3777
Switzerland 00800 2255 4835*
USA 1 800 833 9200

* European toll-free number. If not accessible, call: +41 52 675 3777

Updated 10 April 2013

For Further Information. Tektronix maintains a comprehensive, constantly expanding collection of application notes, technical briefs and other resources to help engineers working on the cutting edge of technology. Please visit www.tektronix.com.

Copyright © Tektronix, Inc. All rights reserved. Tektronix products are covered by U.S. and foreign patents, issued and pending. Information in this publication supersedes that in all previously published material. Specification and price change privileges reserved. TEKTRONIX and TEK are registered trademarks of Tektronix, Inc. All other trade names referenced are the service marks, trademarks, or registered trademarks of their respective companies.

19 Apr 2013

51W-19997-8