


THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
AD	00	P	LTR	DESCRIPTION	DATE	DWN
			E	EC 0G3C 0645 04	10MAR05	BSV
						DFR



- 1 CUT OUTS ON BOX AT MANUFACTURER'S OPTION
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS)
- 3 POINT OF MEASUREMENT FOR PLATING THICKNESS (OUTSIDE BOTTOM)
- 4 ROHS 2002/95/EC COMPLIANT



.000030 GOLD IN CONTACT AREA, .000050 MIN TIN IN AREA SHOWN, ALL OVER .000050 NICKEL.	5-104449-6
.000030 GOLD IN CONTACT AREA .000050 MIN TIN-PLATED IN AREA SHOWN, ALL OVER .000050 NICKEL	102449-3
PLATING	PART NO LOOSE PIECE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.S.VISWESWARA 10MAR05	tyco Tyco Electronics Corporation Electronics Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK D.F.RHODE		
	0 PLC ± -	APVD -	NAME CONTACT-MOD IV MASS TERMINATION AMPMODU #20-#22 AWG WIRE SIZE	
	1 PLC ± -	PRODUCT SPEC -		
	2 PLC ± -	APPLICATION SPEC -	SIZE A2	CAGE CODE 00779
	3 PLC ± -	WEIGHT -	DRAWING NO C=102449	RESTRICTED TO -
MATERIAL -	FINISH -	CUSTOMER DRAWING	SCALE 10:1	SHEET 1 OF 1
			REV E	