




STRIP MATERIAL NUMBER	FINISH
84590-0022	OVERALL NICKEL 80µ" MINIMUM





SECTION Z-Z



SECTION Y-Y

PAYOFF DIRECTION



WIRE INSULATION O.D. RANGE .075-.150 / 1.91-3.81

NOTES:

1. MATERIAL: COPPER ALLOY .0120/0.305 THICK.
2. FINISH: SEE CHART.
3. STRIP TERMINALS ARE REELED AS SHOWN ABOVE, 3000 PARTS PER REEL.
4. TERMINAL FOR USE WITH SERIES XRC CONNECTOR ASSEMBLIES.
5. ALL DIMENSIONS ARE REFERENCE.
6. ALL MATERIALS AND FINISHES ARE ROHS COMPLIANT.

UPDATE NOTES & TABLE EC NO: WNA2008-0139 DRAWN: WLEUNG 2008/07/26 CHKD: RDEROSS 2008/04/21 APPR: RDEROSS 2008/04/24	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION 		
				mm	INCH	DRAWN BY	DATE	TITLE	CONTACT PIN, 14-18 AWG, (F) MOLEX MOLEX INCORPORATED		
			4 PLACES	± ---	± ---	RSTONE	10/18/04				
			3 PLACES	± ---	± .010	CHECKED BY	DATE				
			2 PLACES	± 0.25	± .02	APLAZA	10/18/04				
			1 PLACE	± 0.5	± ---	APPROVED BY	DATE		MOLEX MOLEX INCORPORATED		
			ANGULAR ± 1 °		LROTHAUS	10/18/04					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
						SEE CHART		SD-84590-003		1 OF 1	
						SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			