








FCIconnect.com

Copyright FCI


view shown without grounding and plastic pin



Detail of grounding strip



PC card drilling dimensions(after plating)
(thickness 1.60 ±0.25 mm)



TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	18.00	16.21	10.96	D09S82C7GX8C
15	39.14	33.32	26.32	24.54	19.18	D15S82C7GX8C

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	18.00	16.21	10.96	D09S82C7GX8CLF
15	39.14	33.32	26.32	24.54	19.18	D15S82C7GX8CLF

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code				surface	tolerance	projection	product family			
-				ISO 1302	ISO 406 ISO 1101		D-SUB			
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM	title			
G	ELX-I-18050	MP	2014/06/23	angles	linear					
				0°±2°						
				dr	PESSON	1997/09/08	dwg no			
				engr	MITHUN PAUL	2014/06/23				
				chr	ALIAS BABU	2014/06/23				
				appd	BIJU K PAUL	2014/06/23	sheet 1 of 1			
sheet	revision	G								
index	sheet	1								
							C01-8646-0557			
							A3			
							type			
							Product Customer Drawing			