




ETFE // H-WZT & H-WZ

ETFE insulated wire wrap wires
Intended for use as internal wiring of equipment

Description	Conductor					Finished wire					
H-WZT HSA	Silver Plated High Strength Copper Alloy (HSA)					ETFE			Weight	Amps	
	Size		Stranding	Resistance	Wire	Core	Tolerance				
300 / 500V AC U ₀ /U	AWG	mm ²	# x mm	Ω/km	Nom Ø	Nom Ø	Min Ø	Max Ø	Nom g/m	@ 40°C	Article Number
H-WZT 3201 HSA	32	0.04	1 x 0.203	627	0.20	0.47	0.45	0.49	0.5	3	564cc3201
H-WZT 3001 HSA	30	0.05	1 x 0.254	400	0.25	0.55	0.47	0.58	0.8	4	564cc3001
H-WZT	Silver Plated Oxygen Free Copper (SPOFHC)					ETFE			Weight	Amps	
	Size		Stranding	Resistance	Wire	Core	Tolerance				
300 / 500V AC U ₀ /U	AWG	mm ²	# x mm	Ω/km	Nom Ø	Nom Ø	Min Ø	Max Ø	Nom g/m	@ 40°C	Article Number
H-WZT 3201	32	0.04	1 x 0.203	517	0.20	0.47	0.45	0.49	0.5	3	567cc3201
H-WZT 3001	30	0.05	1 x 0.254	330	0.25	0.55	0.47	0.58	0.8	4	567cc3001
H-WZT 2801	28	0.08	1 x 0.320	208	0.32	0.62	0.57	0.67	1.1	6	567cc2801
H-WZT 2601	26	0.13	1 x 0.404	131	0.40	0.70	0.65	0.75	1.6	8	567cc2601
H-WZT 2401	24	0.20	1 x 0.511	81.5	0.51	0.81	0.76	0.85	2.3	10	567cc2401
H-WZT 2201	22	0.32	1 x 0.643	51.5	0.64	0.94	0.89	0.98	3.5	14	567cc2201
H-WZT 2001	20	0.51	1 x 0.813	32.2	0.81	1.10	1.06	1.15	5.4	18	567cc2001
H-WZ	Silver Plated Oxygen Free Copper (SPOFHC)					ETFE			Weight	Amps	
	Size		Stranding	Resistance	Wire	Core	Tolerance				
600 / 1000V AC U ₀ /U	AWG	mm ²	# x mm	Ω/km	Nom Ø	Nom Ø	Min Ø	Max Ø	Nom g/m	@ 40°C	Article Number
H-WZ 2601	26	0.13	1 x 0.404	131	0.40	0.86	0.81	0.91	1.9	8	568cc2601
H-WZ 2401	24	0.20	1 x 0.511	81.5	0.51	0.96	0.91	1.01	2.7	11	568cc2401
H-WZ 2201	22	0.32	1 x 0.643	51.5	0.64	1.09	1.04	1.14	3.9	14	568cc2201
H-WZ 2001	20	0.51	1 x 0.813	32.2	0.81	1.26	1.21	1.31	5.8	19	568cc2001

Core identification: Replace 'cc' in the article number with 2 digits below to select from available colours											
00: Black	11: Brown	22: Red	33: Orange	44: Yellow	55: Green	66: Blue	77: Violet	88: Grey	99: White	29: Pink	89: Clear
Characteristics and key properties											
	RoHS 2011/65/EU	REACH EC No. 1907/2006	LVD 2014/35/EU						Low smoke generation	Flame retardant	+150°C High temp
										Current rating in free air to IEC 60287	-65°C Low temp

Data indicates nominal values in millimetres (mm) unless otherwise stated.
DISCLAIMER: Information is indicative and cannot be considered a binding representation or warranty for products and their use. Valid at the time of publication, it is subject to change without notice.