


LCR CAPACITORS

Ref 78.

LOW LOSS
POLYSTYRENE
CAPACITORS
TYPE : FSC / EX



N.B. support must be given at the ends of the resin before preforming

CAPACITANCE	L = mm	D = mm	WORKING VOLTAGE	
				@ 50Hz
47p - 200p	12.5	5.00	630V DC	250V AC
201p - 360p	12.9	5.00	630V DC	250V AC
361p - 560p	12.9	4.50	630V DC	250V AC
561p - 680p	12.9	5.00	630V DC	250V AC
681p - 750p	12.9	5.00	630V DC	250V AC
751p - 820p	12.9	4.50	250V DC	125V AC
821p - 910p	12.9	4.50	250V DC	125V AC
911p - 1 n	12.9	4.50	250V DC	125V AC
1n1 - 1n6	12.5	5.00	160V DC	80V AC
1n61 - 2n7	12.5	4.75	160V DC	80V AC
2n71 - 3n9	12.9	5.00	160V DC	80V AC
3n91 - 6n2	17.0	5.00	160V DC	80V AC
6n21 - 7n5	17.0	5.50	160V DC	80V AC
7n51 - 8n2	17.0	6.00	160V DC	80V AC
8n21 - 10n	17.0	5.00	160V DC	80V AC
10n1 - 15n	17.0	5.50	63V DC	40V AC
15n1 - 18n	17.0	6.00	63V DC	40V AC
18n1 - 24n	17.0	6.50	63V DC	40V AC
24n1 - 30n	17.0	7.00	63V DC	40V AC
30n1 - 36n	17.0	7.50	63V DC	40V AC
36n1 - 39n	17.0	8.00	63V DC	40V AC
39n1 - 51n	17.0	10.00	63V DC	40V AC
51n1 - 68n	22.0	8.50	63V DC	40V AC
68n1 - 82n	22.0	9.50	63V DC	40V AC
82n1 - 100n	22.0	10.00	63V DC	40V AC

CAPACITANCE RANGE	47 pf - 51 nf
CAPACITANCE TOLERANCE	+ 1%, +2%, +5%, +10% (MIN 1.5 pf)
TEST VOLTAGE	2 X WORKING VOLTAGE
POWER FACTOR	≤0.0005 @ 1KHz ALL VALUES ≤0.0007 @ 100KHz ALL VALUES ≤0.0010 @ 1MKHz 47pf - 1nf
INSULATION RESISTANCE	>10 ⁵ MegOhm
TEMPERATURE RANGE	-40°c / +85°c
TEMPERATURE COEFFICIENT	-110 + 60ppm/°c

ISSUE 6
APRIL 2003