



100 W

DC- 2 GHz

N

COAXIAL ATTENUATOR

issue
20.dec.95

Page
1 / 2

R F CHARACTERISTICS

FREQUENCY RANGE : DC - 2 GHz
IMPEDANCE : 50 Ohms
ATTENUATION - NOMINAL : 3 dB

FREQUENCY	DC- 1 GHz	1 - 2 GHz
V.S.W.R (dB)	<= 1.10	<= 1.25
DEVIATION (dB)	+1.0 / -1.0	+1.0 / -1.0


PEAK POWER at 25°C (1μs,1%.) : 5 kW
AVERAGE POWER at 25°C : 100 W

MECHANICAL CHARACTERISTICS

CONNECTORS : N male/female per MIL-C 39012
WEIGHT : < 1050 g

ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE RANGE (°C) : -55 , +125
STORAGE TEMPERATURE RANGE (°C) : -55 , +125



CREATION

N° :
PEN/EP:CAT
Name:KL
Date:30.oct.91
APP.:VE

20.dec.95
ISSUE

New drawing and cotation.
REVISIONS

MLG
NAME

VE
APPR.

RADIAL[®]


101. rue P. Hoffmann -Z.I Ouest-
93116 ROSNY/BOIS Cedex-FRANCE
Phone:33(1)49353535
Fax :33(1)48546363
Tvx RADIA 235220F

R417703118

issue
20 . dec . 95

Page
2 / 2

DRAWING



General tolerances:
+/- 0.8 mm