




REV BL



SUFFIX	TAIL LENGTH "A"	TAIL WIDTH "B"
-X1	.120 [3.05]	.020 [.51]
-X3	.075 [1.91]	.016 [.41]

FIG. 1
-X1: THROUGH HOLEFIG. 2
-X2: SURFACE MOUNT
DIFFERENT AS SHOWN,
OTHERWISE SAME AS FIG. 1.

UNLESS OTHERWISE NOTED

TOLERANCES ARE:

ONE PLACE DECIMALS $\pm .1$ [3] THREE PLACE DECIMALS $\pm .005$ [.13]
TWO PLACE DECIMALS $\pm .01$ [.3] FOUR PLACE DECIMALS $\pm .0020$ [.051]

ANGLES
 $\pm 2^\circ$

TITLE: .050 X .050
CUTTABLE SOCKET STRIP
DOUBLE ROW ASSEMBLY

DWG NO:

SFMC-1XX-XX-XX-D-XX

SHEET 1 OF 2

SFMC-1XX-XX-XX-D-XX

NO. OF POSITIONS
ALL POSITIONS AVAILABLE
-02 THRU -50
USE BODY: (SFMC-50-D)

LEAD STYLE

- 01: THROUGH HOLE (SEE FIGURE 1)
USE CONTACT: (C-44-01-XX)
- 02: SURFACE MOUNT (SEE FIGURE 2)
USE CONTACT: (C-44-02-XX)
- 03: STRAIGHT MODIFIED (SEE FIGURE 1)
USE CONTACT: (C-44-03-XX)
- L1: THROUGH HOLE (LOW INSERTION) (SEE FIGURE 1)
USE CONTACT: (C-61-01-XX)
- L2: SURFACE MOUNT (LOW INSERTION) (SEE FIGURE 2)
USE CONTACT: (C-61-02-XX)
- L3: STRAIGHT MODIFIED (LOW INSERTION) (SEE FIGURE 1)
USE CONTACT: (C-61-03-XX)
- T1: THROUGH HOLE (PHOS BRONZE) (SEE FIGURE 1)
USE CONTACT: (C-119-01-XX)
- T2: SURFACE MOUNT (PHOS BRONZE) (SEE FIGURE 2)
USE CONTACT: (C-119-02-XX)

OPTIONS

- (LEAVE BLANK FOR STANDARD)
- P: PICK AND PLACE PAD (SEE FIGURE 3, SHT 2)
USE PPP-02 (5 POSITIONS MINIMUM)
- TR: TAPE & REEL (SEE FIG. 4, SHT 2)
- K: POLYAMIDE FILM PAD (.005 [.13]
THICKNESS WITH SILICONE ADHESIVE)
(SEE FIG. 4) (USE K-500-300)
(4 POS MIN)

BODY SPECIFICATION

-D: DOUBLE ROW

PLATING SPECIFICATION


- S: SELECTIVE - SPECIFY -S IN PLATING SUFFIX -X
- P: GOLD FLASHED PALLADIUM NICKEL - SPECIFY -P IN PLATING SUFFIX -X
- F: FLASH SELECTIVE GOLD - SPECIFY -F IN PLATING SUFFIX -X
- H: HEAVY GOLD - SPECIFY -H IN PLATING SUFFIX -X
(ONLY AVAILABLE ON -02, -L2, & -T2 LEAD STYLES)
- FM: FLASH SELECTIVE, MATTE TIN TAIL - SPECIFY -FM IN PLATING SUFFIX -X
- SM: SELECTIVE, MATTE TIN TAIL - SPECIFY -SM IN PLATING SUFFIX -X
- L: LIGHT SELECTIVE GOLD, MATTE TIN TAIL - SPECIFY -L IN PLATING SUFFIX -X

TABLE 2

LEAD STYLE & OPTION	PACKAGING TUBE	PLUG
-X1, -X3 (SEE NOTE 5)	PT-1-24-15-09	TP-24-02
-X2 (SEE NOTE 6)	PT-1-24-14-09	TP-24-02
-X2-K (SEE NOTE 6)	PT-1-24-14-09	TP-24-02
-X2-P (SEE NOTE 6)	PT-1-24-01-38	TP-24
-X1-K (SEE NOTE 6)	PT-1-24-02-29	TP-24
-X1-P, -X3-P (SEE NOTE 5)	PT-1-24-01-09	TP-24

NOTES:

1. MIN. PUSHOUT FORCE: .5 lb.
2. COPLANARITY: .004 [.10] = POS 02 THRU 26
.006 [.15] = POS 27 THRU 50
3. (C) REPRESENTS CRITICAL DIMENSION.
4. USE SFMC-50-D BODY.
5. PACKAGE ALL POSITIONS OF THIS LEAD STYLE IN TUBES.
6. PACKAGE ONLY POSITIONS -04 THRU -50 IN TUBES:
LAYER PACKAGE POSITIONS -02 THRU -05.
7. CUT FLASH TO BE .010 MAX WITH NO FLASH EXTENDING BELOW LEADS OR IN HOLES OF BODY.
8. MAX HEIGHT VARIATION BETWEEN ANY TWO PINS TO BE .008 [.08].
9. PINS CAN BE ORIENTED IN ANY DIRECTION; BOTH ROWS MUST FACE SAME WAY.



NOTE: "R" = USED MEASURED DIMENSION (REF)
"S" = $\{("R" - .1575 [4.00]) / 2\} \pm .020 [.51]$

MATERIAL:
BODY:
VECTRA E130
COLOR: BLACK

CONTACTS:
C-44 & C-66:
#25 BeCu, 1/2 HARD
AGE HARDENED
C-119
PHOS BRONZE 521

EXISPROD\ASSEMBLY\050
SFMC-ASM

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY:
BRATCHER 10-5-94

SFMC-1XX-XX-XX-D-XX
SHEET 1 OF 2

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.