


THIS DRAWING IS A CONTROLLED DOCUMENT  
REV 17579

Restricted to: General Release

USED ON




#### Left Side

Connector(s): MT-RJ SECURE (No Pins)

Mode: MM

Housing Color: Blue

Geom. Spec: 115-1215



VIEW C-C  
NOT TO SCALE

#### Fiber Path

Fiber A - ——— - B  
Fiber B - ——— - A

#### Notes:

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Label 2 will not be present on any cable assembly less than 5 meters long.
- 3 Includes dust caps (not shown on print).

#### Right Side

Connector(s): SC-Duplex

Mode: MM

Housing Color: Beige


Geom. Spec: N/A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC  
CE  
DIST  
16

CAC Customer Layout Rev: D

|   |     |             |               |           |    |      |  |
|---|-----|-------------|---------------|-----------|----|------|--|
|   |     |             |               |           |    |      |  |
|   | B   | Rev Per EC# | ECR-06-020123 | 9/21/2006 | -  | MK   |  |
| P | LTR | REVISION    | RECORD        | DATE      | DN | APVD |  |



DIMENSIONS:  
meters

Customer Print

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

9 PLC ± .  
1 PLC ± .  
2 PLC ± .  
3 PLC ± .  
4 PLC ± .

|            |                                                                                         |          |            |
|------------|-----------------------------------------------------------------------------------------|----------|------------|
| DIN        | Cable Assy Configurator                                                                 | MATERIAL | HEAT TREAT |
| CHK        | Michael Kepko                                                                           |          |            |
| APVD       | Michael Kepko                                                                           |          |            |
| NAME       | FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, MT-RJ SECURE (No Pins) to SC-Duplex |          |            |
| SCALE      | NTS                                                                                     | SIZE     | A2         |
| DRAWING NO | C- 6754413                                                                              |          | SHEET      |
| 1 of 3     |                                                                                         |          | REV        |
|            |                                                                                         |          | B          |

**AMP** Tyco Electronics, Inc.  
Harrisburg, PA 17105-3608

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA

LOC  
CE  
DIST  
16

CAC Customer Layout Rev: D

Restricted to: General Release

USED ON

86-40

THIS DRAWING IS A CONTROLLED DOCUMENT.

| Part #      | L (meters)      | L (feet)        | MT-RJ SECURE (No Pins), Blue |         |  | SC-Duplex, Beige |         |  |
|-------------|-----------------|-----------------|------------------------------|---------|--|------------------|---------|--|
|             |                 |                 | IL (dB)                      | RL (dB) |  | IL (dB)          | RL (dB) |  |
| 0-6754413-1 | 0.950 - 1.050   | 3.11 - 3.44     | 0.5                          | 20      |  | 0.5              | -       |  |
| 0-6754413-2 | 1.950 - 2.050   | 6.39 - 6.72     | 0.5                          | 20      |  | 0.5              | -       |  |
| 0-6754413-3 | 2.950 - 3.050   | 9.67 - 10.00    | 0.5                          | 20      |  | 0.5              | -       |  |
| 0-6754413-4 | 3.920 - 4.080   | 12.86 - 13.38   | 0.51                         | 20      |  | 0.51             | -       |  |
| 0-6754413-5 | 4.920 - 5.080   | 16.14 - 16.66   | 0.51                         | 20      |  | 0.51             | -       |  |
| 0-6754413-6 | 5.920 - 6.080   | 19.42 - 19.94   | 0.51                         | 20      |  | 0.51             | -       |  |
| 0-6754413-7 | 6.920 - 7.080   | 22.70 - 23.22   | 0.51                         | 20      |  | 0.51             | -       |  |
| 0-6754413-8 | 7.920 - 8.080   | 25.98 - 26.50   | 0.51                         | 20      |  | 0.51             | -       |  |
| 0-6754413-9 | 8.850 - 9.150   | 29.03 - 30.01   | 0.51                         | 20      |  | 0.51             | -       |  |
| 1-6754413-0 | 9.850 - 10.150  | 32.31 - 33.30   | 0.52                         | 20      |  | 0.52             | -       |  |
| 1-6754413-1 | 10.850 - 11.150 | 35.59 - 36.58   | 0.52                         | 20      |  | 0.52             | -       |  |
| 1-6754413-2 | 11.850 - 12.150 | 38.87 - 39.86   | 0.52                         | 20      |  | 0.52             | -       |  |
| 1-6754413-3 | 12.850 - 13.150 | 42.15 - 43.14   | 0.52                         | 20      |  | 0.52             | -       |  |
| 1-6754413-4 | 13.850 - 14.150 | 45.43 - 46.42   | 0.52                         | 20      |  | 0.52             | -       |  |
| 1-6754413-5 | 14.850 - 15.150 | 48.72 - 49.70   | 0.52                         | 20      |  | 0.52             | -       |  |
| 1-6754413-6 | 15.840 - 16.160 | 51.96 - 53.01   | 0.52                         | 20      |  | 0.52             | -       |  |
| 1-6754413-7 | 16.830 - 17.170 | 55.21 - 56.33   | 0.53                         | 20      |  | 0.53             | -       |  |
| 1-6754413-8 | 17.820 - 18.180 | 58.46 - 59.64   | 0.53                         | 20      |  | 0.53             | -       |  |
| 1-6754413-9 | 18.810 - 19.190 | 61.71 - 62.95   | 0.53                         | 20      |  | 0.53             | -       |  |
| 2-6754413-0 | 19.800 - 20.200 | 64.96 - 66.27   | 0.53                         | 20      |  | 0.53             | -       |  |
| 2-6754413-1 | 20.790 - 21.210 | 68.20 - 69.58   | 0.53                         | 20      |  | 0.53             | -       |  |
| 2-6754413-2 | 21.780 - 22.220 | 71.45 - 72.90   | 0.53                         | 20      |  | 0.53             | -       |  |
| 2-6754413-3 | 22.770 - 23.230 | 74.70 - 76.21   | 0.53                         | 20      |  | 0.53             | -       |  |
| 2-6754413-4 | 23.760 - 24.240 | 77.95 - 79.52   | 0.54                         | 20      |  | 0.54             | -       |  |
| 2-6754413-5 | 24.750 - 25.250 | 81.20 - 82.84   | 0.54                         | 20      |  | 0.54             | -       |  |
| 2-6754413-6 | 25.740 - 26.260 | 84.44 - 86.15   | 0.54                         | 20      |  | 0.54             | -       |  |
| 2-6754413-7 | 26.730 - 27.270 | 87.69 - 89.46   | 0.54                         | 20      |  | 0.54             | -       |  |
| 2-6754413-8 | 27.720 - 28.280 | 90.94 - 92.78   | 0.54                         | 20      |  | 0.54             | -       |  |
| 2-6754413-9 | 28.710 - 29.290 | 94.19 - 96.09   | 0.54                         | 20      |  | 0.54             | -       |  |
| 3-6754413-0 | 29.700 - 30.300 | 97.44 - 99.40   | 0.55                         | 20      |  | 0.55             | -       |  |
| 3-6754413-1 | 30.690 - 31.310 | 100.68 - 102.72 | 0.55                         | 20      |  | 0.55             | -       |  |
| 3-6754413-2 | 31.680 - 32.320 | 103.93 - 106.03 | 0.55                         | 20      |  | 0.55             | -       |  |
| 3-6754413-3 | 32.670 - 33.330 | 107.18 - 109.35 | 0.55                         | 20      |  | 0.55             | -       |  |
| 3-6754413-4 | 33.660 - 34.340 | 110.43 - 112.66 | 0.55                         | 20      |  | 0.55             | -       |  |
| 3-6754413-5 | 34.650 - 35.350 | 113.68 - 115.97 | 0.55                         | 20      |  | 0.55             | -       |  |
| 3-6754413-6 | 35.640 - 36.360 | 116.92 - 119.29 | 0.55                         | 20      |  | 0.55             | -       |  |
| 3-6754413-7 | 36.630 - 37.370 | 120.17 - 122.60 | 0.56                         | 20      |  | 0.56             | -       |  |
| 3-6754413-8 | 37.620 - 38.380 | 123.42 - 125.91 | 0.56                         | 20      |  | 0.56             | -       |  |
| 3-6754413-9 | 38.610 - 39.390 | 126.67 - 129.23 | 0.56                         | 20      |  | 0.56             | -       |  |
| 4-6754413-0 | 39.600 - 40.400 | 129.92 - 132.54 | 0.56                         | 20      |  | 0.56             | -       |  |
| 5-6754413-0 | 49.500 - 50.500 | 162.40 - 165.68 | 0.58                         | 20      |  | 0.58             | -       |  |

| Qty | U of M | Description                                            | Item No. |
|-----|--------|--------------------------------------------------------|----------|
| 1   | piece  | DUST COVER, MT-RJ                                      | 1        |
| 1   | piece  | SPRING, MT-RJ, 3.8 DESIGN                              | 2        |
| 1   | piece  | PIN KEEPER, 3.8MM                                      | 3        |
| 1   | piece  | MT-RJ, SPRING PUSH, UNIVERSAL                          | 4        |
| 1   | piece  | CRIMP EYELET, MT-RJ                                    | 5        |
| 1   | piece  | MT-RJ Keyed Connector Housing - Blue                   | 6        |
| 2   | piece  | LC, SC, FC Straight Boot, Beige                        | 7        |
| 1   | piece  | MT-RJ FERRULE, THERMOPLAST,MM                          | 8        |
| 2   | piece  | SC Simplex Housing, Beige                              | 9        |
| 2   | piece  | 2.5mm ferrule cover                                    | 10       |
| AR  | meter  | 2 fiber, XG-50/125, 1.8mm, Twinzip, Aqua, OFNR (Riser) | 11       |
| 1   | piece  | MT-RJ TwinZip Bend Limiting Boot, Beige                | 12       |
| 2   | piece  | SC Duplex Clip                                         | 13       |
| 2   | piece  | Eyelet/Shrink tube assembly - White                    | 14       |
| 2   | piece  | CONN SUBASSY, MM, SC 1.6MM                             | 15       |
| 2   | piece  | Trace Label                                            | 16       |

|   |             |                 |           |     |      |
|---|-------------|-----------------|-----------|-----|------|
|   |             |                 |           |     |      |
|   |             |                 |           |     |      |
| B | Rev Per EC# | ECR-06-020123   | 8/21/2006 | -   | MK   |
| P | LTR         | REVISION RECORD | DATE      | DIN | APVD |

|                       |  |                                           |     |
|-----------------------|--|-------------------------------------------|-----|
| DIMENSIONS:<br>meters |  | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED: |     |
|                       |  | Ø P.L.C.                                  | ± . |
|                       |  | 1 P.L.C.                                  | ± . |
|                       |  | 2 P.L.C.                                  | ± . |
|                       |  | 3 P.L.C.                                  | ± . |
|                       |  | 4 P.L.C.                                  | ± . |


|                                                                                                    |               |                                                                |                 |          |
|----------------------------------------------------------------------------------------------------|---------------|----------------------------------------------------------------|-----------------|----------|
| DIN<br>Cable Assy Configurator                                                                     |               | MATERIAL<br>-                                                  | HEAT TREAT<br>- |          |
| OK                                                                                                 | Michael Kepko | <b>AMP</b> Tyco Electronics, Inc.<br>Harrisburg, PA 17105-3608 |                 |          |
| APVD                                                                                               | Michael Kepko |                                                                |                 |          |
| NAME<br>FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, MT-RJ<br>SECURE (No Pins) to SC-Duplex |               |                                                                |                 |          |
| SCALE<br>NTS                                                                                       | SIZE<br>A2    | DRAWING NO<br>C- 6754413                                       | SHEET<br>2 of 3 | REV<br>B |

Customer Print

8 7 6 5 4 3 2 1

## Label 1


Per specification 107-1645-1



This label is used on all lengths on this drawing.

## Label 2

Per specification 107-1645-1



This label is used on all lengths on this drawing.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC  
CE  
DIST  
16

CAC Customer Layout Rev: D

|   |     |                 |               |           |     |      |  |
|---|-----|-----------------|---------------|-----------|-----|------|--|
|   |     |                 |               |           |     |      |  |
|   |     |                 |               |           |     |      |  |
|   | B   | Rev Per EC#     | ECR-06-020123 | 9/21/2006 | -   | MK   |  |
| P | LTR | REVISION RECORD |               | DATE      | DIN | APVD |  |

| DIMENSIONS: |     | TOLERANCES UNLESS OTHERWISE SPECIFIED: |   |
|-------------|-----|----------------------------------------|---|
| meters      |     |                                        |   |
| Ø           | PLC | ±                                      | - |
| □           | PLC | ±                                      | - |
| □           | PLC | ±                                      | - |
| □           | PLC | ±                                      | - |
| □           | PLC | ±                                      | - |

Customer Print

|                             |               |                                                                                       |            |     |
|-----------------------------|---------------|---------------------------------------------------------------------------------------|------------|-----|
| DIN Cable Assy Configurator |               | MATERIAL                                                                              | HEAT TREAT |     |
| OK                          | Michael Kepko |  |            |     |
| APVD                        | Michael Kepko |                                                                                       |            |     |
| NAME                        |               |                                                                                       |            |     |
| SCALE                       | SIZE          | DRAWING NO.                                                                           | SHEET      | REV |
| NTS                         | A2            | C- 6754413                                                                            | 3 of 3     | B   |

8

7

6

5

4

3

2

1