





REV.	DATE	DESCRIPTION
A	02/24/03	UPDATE DRAWING FORMAT
B	06/30/07	REVISE BODY LENGTH, CONTACT PIN, FERRULE DIMENSIONS



NOTE:
1. CRIMPED FERRULE HEX CRIMP SIZE .213"
2. CRIMPED CONTACT PIN HEX CRIMP SIZE .068"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex TNC REVERSE POLARITY CRIMP PLUG (FOR RG-58C/U CABLE) 122108RP DWG. NO. 122108RP.DWGREV. BSIZE ASCALE NADWG. NO. 122108RP.DWGREV. BSIZE ASCALE NA			
8						DRAWN G.R.S.	06/30/07				
7						CHECKED					
6						ISSUED					
5	FERRULE	COPPER	NICKEL	1		SHEET 1 OF 1					
4	GASKET	RUBBER	RED	1				PART DESCRIPTION			
3	CONTACT PIN	PHOS. BRONZE	GOLD	1				PART NO.			
2	INSULATOR	TEFLON	NATURAL	1				122108RP			
1	SHELL/BODY	BRASS	NICKEL	1							
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE C:/122/122108RP.DWG					