





20 19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1

NOTES:

- 1 THESE HOUSINGS ARE FOR USE WITH THE 1457-•• TERMINALS AND MAY BE SUBDIVIDED BY USING THE 1461-K KEY.
- 2 THE HOUSINGS ARE ONLY AVAILABLE IN 5, 10, 15, AND 20 CIRCUIT SIZES.
- 3 PRODUCT SPECIFICATION PS 50-36 APPLIES.
- 4 THESE HOUSINGS CONFORM TO U.L. AND C.S.A. REQUIREMENTS.
- 5 .060/(1.52) HIGH RAISED NUMERALS.
- 6 .125/(3.18) HIGH RECESSED NUMERALS ON A MATTE BACKGROUND.
- 7 .09/(2.3) HIGH INK STAMPED NUMERALS.




VIEW A-A



MATERIAL:

POLYESTER, UNFILLED, 94V-0.
COLOR: BLACK.
(REF.: SMES 128C-D)



MODIFY COUR OUTS EC NO: UCP2005-2756 DRAWN BY: DRWNS BARBA 2005/09/29 CHECKED BY: CHYD BARKER 2005/10/10 APPROVED BY: APPR: SMILLER 2005/10/12	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)				DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
		mm		INCH		DRAWN BY DATE		TITLE			
		4 PLACES ±		---		AFG 95/12/18		HOUSING, COMMONING			
		3 PLACES ±		.010		CHECKED BY DATE		[.090/(2.29) OFFSET]			
		2 PLACES ±		.014		RHR 95/12/18					
		1 PLACE ±		.035		APPROVED BY DATE					
		ANGULAR ±1/2°				GWF 95/12/18		MOLEX MOLEX INCORPORATED			
		DRAFT WHERE APPLICABLE				MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
		MUST REMAIN WITHIN DIMENSIONS				SEE TABLE		SD-1461-*		3 OF 4	
						SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

19 18 17 16 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1

	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1				
	PART NO.	ENG. NO.	NO. CKTS.	DIM. A	DIM. B	DIM. C	DIM. D	INK STAMPED HOUSINGS								SPECIAL INK STAMPED HOUSINGS CHART								
	07-01-8203	1461-20W	20	3.50 (88.9)	3.63 (92.2)	4.00 (101.6)	4.24 (107.7)	BEFORE INK STAMP PART NO.	ENG. NO.	AFTER INK STAMP PART NO.	ENG. NO.	NO. CKTS.	DIM. A	DIM. B	DIM. C	DIM. D	BEFORE INK STAMP PART NO.	ENG. NO.	AFTER INK STAMP PART NO.	ENG. NO.	NO. CKTS.	CIRCUIT NUMERALS		
M								007-01-8202	1461-200	007-01-8201	1461-20E	20	3.50 (88.9)	3.63 (92.2)	4.00 (101.6)	4.24 (107.7)	007-01-8102	1461-100	007-01-8104	1461-10-1F	10	11 THRU 20		
																			007-01-8105	1461-10-2F	10	21 THRU 30		
																			007-01-8106	1461-10-3F	10	31 THRU 40		
L	07-01-8153	1461-15W	15	2.62 (66.5)	2.75 (69.9)	3.13 (79.5)	3.37 (85.6)	007-01-8152	1461-150	007-01-8151	1461-15E	15	2.62 (66.5)	2.75 (69.9)	3.13 (79.5)	3.37 (85.6)								
	07-01-8103	1461-10W	10	1.750 (44.45)	1.875 (47.63)	2.250 (57.15)	2.49 (63.2)	007-01-8102	1461-100	007-01-8101	1461-10E	10	1.750 (44.45)	1.875 (47.63)	2.250 (57.15)	2.49 (63.2)	007-01-8102	1461-150	007-01-8104	1461-15-1F	15	16 THRU 30		
																			007-01-8105	1461-15-2F	15	31 THRU 45		
	07-01-8053	1461-5W	5	.875 (22.23)	1.000 (25.40)	1.375 (34.93)	1.615 (41.02)	007-01-8052	1461-50	007-01-8051	1461-5E	5	.875 (22.23)	1.000 (25.40)	1.375 (34.93)	1.615 (41.02)			007-01-8106	1461-15-3F	15	46 THRU 60		
																			007-01-8202	1461-200	007-01-8204	1461-20-1F	20	21 THRU 40
																			007-01-8205	1461-20-2F	20	41 THRU 60		
																			007-01-8206	1461-20-3F	20	61 THRU 80		