


SURFACE MOUNT LED LAMP

0805 Chip Type - Water Clear

PACKAGE DIMENSIONS




NOTE:
Dimensions are in inches (mm).

HER
Yellow
Green
AlGaAs Red

QTLP630C-2
QTLP630C-3
QTLP630C-4
QTLP630C-7

FEATURES

- Ultra-miniature and extremely low profile
- Industrial standard footprint
- Wide viewing angle of 140°
- Water clear optics
- Moisture-proof packaging



DESCRIPTION

These surface mount lamps are designed to fit industry standard profile and footprint for ultra-miniature chip type 0805. The low profile and 140° viewing angle make this chip type LED ideal for panel illumination, push-button backlighting and membrane switch applications.

ABSOLUTE MAXIMUM RATINGS (T_A = 25°C unless otherwise specified)

Parameter	HER QTLP630C-2	Yellow QTLP630C-3	Green QTLP630C-4	AlGaAs Red QTLP630C-7	Units
Continuous Forward Current - I _F	30	20	30	30	mA
Peak Forward Current - I _F (f = 1.0 KHz, Duty Factor = 1/10)	160	160	160	160	mA
Reverse Voltage - V _R (I _R = 10 μA)	5	5	5	5	V
Power Dissipation - P _D	100	85	100	100	mW
Operating Temperature - T _{OPR}	-40 to +100				°C
Storage Temperature - T _{STG}	-40 to +100				°C
Lead Soldering Time - T _{SOL}					°C
Wave	260 for 5 sec				
Reflow	260 for 10 sec				

SURFACE MOUNT LED LAMP

0805 Chip Type - Water Clear

HER	QTLP630C-2
Yellow	QTLP630C-3
Green	QTLP630C-4
AlGaAs Red	QTLP630C-7

ELECTRICAL / OPTICAL CHARACTERISTICS (T_A = 25°C)

Part Number	HER QTLP630C-2	Yellow QTLP630C-3	Green QTLP630C-4	AlGaAs Red QTLP630C-7	Condition
Luminous Intensity (mcd)					I _F = 20mA
Minimum	4	5	7	10	
Typical	15	15	20	20	
Forward Voltage (V)					I _F = 20mA
Maximum	2.8	2.8	2.8	2.4	
Typical	2.0	2.0	2.1	1.7	
Peak Wavelength (nm)	635	585	565	660	I _F = 20mA
Spectral Line Half Width (nm)	45	35	30	20	I _F = 20mA
Viewing Angle (°)	140	140	140	140	I _F = 20mA

TYPICAL PERFORMANCE CURVES




Fig. 1 Forward Current vs. Forward Voltage




Fig. 2 Relative Luminous Intensity vs. DC Forward Current

HER
Yellow
Green
AlGaAs Red

QTLP630C-2
QTLP630C-3
QTLP630C-4
QTLP630C-7

TYPICAL PERFORMANCE CURVES




Fig. 3 Relative Intensity vs. Peak Wavelength




Fig. 4 Radiation Diagram





Fig. 5 Current Derating Curve

SURFACE MOUNT LED LAMP


0805 Chip Type - Water Clear

HER	QTLP630C-2
Yellow	QTLP630C-3
Green	QTLP630C-4
AlGaAs Red	QTLP630C-7

RECOMMENDED PRINTED CIRCUIT BOARD PATTERN



RECOMMENDED IR REFLOW SOLDERING PROFILE



DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.