


PROD 4092 CODE	LOC DF	DIST 50	P	F	REVISIONS							
					ZONE	LTR	DESCRIPTION			DATE	APPD	
						N	REV & REDRAWN PER DF-2559			CT	4-90	DE
						P	REV PER 0600-4150-95			CT	8-95	DE

PART NO.	A 	
830614-1	24.00	[609.6]
830614-2	12.00	[304.8]
830614-3	18.00	[457.2]
830614-4	120.00	[3048.0]
830614-5	12.50	[317.5]
830614-6	16.00	[406.4]
830614-7	13.25	[336.5]
830614-8	8.50	[215.9]
830614-9	9.50	[241.3]
1-830614-0	10.00	[254.0]
1-830614-1	14.50	[368.3]
1-830614-2	5.00	[127.0]
1-830614-3	72.00	[1828.8]
1-830614-4	60.00	[1524.0]
1-830614-5	6.00	[152.4]
1-830614-6	36.00	[914.4]
1-830614-7	660.00	[16764.0]
1-830614-8	8.12	[206.2]
1-830614-9	80.00	[2032.0]
2-830614-0	39.38	[1000.3]
2-830614-1	354.31	[8999.5]
2-830614-2	708.62	[17998.9]
2-830614-3	6.50	[165.1]
2-830614-4	14.00	[355.6]
2-830614-5	48.00	[1219.2]
2-830614-6	30.00	[762.0]
2-830614-7	40.00	[1016.0]



- 1

TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = $\pm .12$ [± 3.0]
24 INCHES [609.6] & UP = $\pm 1\%$
2.

MARKED PER MIL-STD-130.
3.

TO MATE WITH AMP LGH-1/2
RECEPTACLE WITH .89 [22.6] BARREL DEPTH.
4.

OPERATING VOLTAGE: 15 KVDC AT 0 TO 70,000 FEET, -55°C TO 125°C.
5.

MIN LEAD LENGTH IS 5 INCHES [127.0].

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm] TOLERANCES ON : 2 PLC DEC $\pm .02$ [0.5] 3 PLC DEC $\pm$ - ANGLES $\pm$ - MATERIAL SEE CALLOUTS FINISH -	DR 12-14-89 C.C.THOMAS	 AMP INCORPORATED Harrisburg, Pa. 17105		
	CHK 4-27-90 D.EABY			
	APPD 4-27-90 D.EABY	NAME LEAD ASS'Y, DBL. END, LGH-1/2L		
	APPD 4-27-90 C.C.THOMAS			
PRODUCT SPEC -	APPLICATION SPEC -	SIZE C	CAGE CODE 00779	DRAWING NO 830614
		SCALE 2:1	SHEET 1 OF 1	