

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREEPORT, ILLINOIS

FED. MFR. CODE 91929

ACTUATOR-SWITCH

CATALOG LISTING

JS-21

(M) JS-21
ISSUE 3

REPLACES

RELEASE NO.

CHECK

10 FEB 56

C.M.T.

CHECK

10 FEB 56

D.L.S.

CHECK

13 FEB 56

CHECK

2 FEB 56

K.F.M.

DRAWN

74-26

JS-21

M

DRAWING
NUMBER


ISSUE

7

REVISIONS

A	CO 9600	K.F.M.	2 FEB 56
B	CO 11211	D. A. W.	5 FEB 57
C	CO 47771	C.J.H.	17 MAY 80
D	CO 79303	DLT	7 MAR 95

.065 MAX. SIDEPLAY






(B)

DETAIL OF LEVER

(2) 2-56 NC HEX. NUT

(2) 2-56 NC x .500^{REF} ROUND HEAD MACHINE SCREW.

(2) LOCKWASHER



DOTTED LINES INDICATE
BASIC SWITCH IN PLACE.

NOTE -

1- SCREWS, NUTS, LOCKWASHERS, AND INSULATOR FURNISHED UNASSEMBLED.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS WITH 13M1 SWITCH INSTALLED

OPERATING FORCE - - - - - 1 OZ. MAX.

RELEASE FORCE - - - - - 4 GRAMS MIN.

DIFFERENTIAL TRAVEL - - - - .031 MAX.

OVERTRAVEL - - - - - .030 MIN.

ELECTRICAL DATA

CONTACT ARRANGEMENT

BREAK DISTANCE

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ±

WEIGHT