

LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
G	14				O	DRAWN PER 0G3A-0027-03	23JAN03	JF DAP

METRIC



DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	 E13288 Listed
26-22 AWG STRANDED	NOT LISTED
 LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

- 1

STAMP 6S AMP APPROX AS SHOWN
6S INDICATES STUD SIZE
- 2

PRELIMINARY – NOT FOR PRODUCTION



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170° C MAX	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -	DR 23JAN03 JR RUTH	YES	53003-4
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS			VOLTAGE RATING: NOT APPLICABLE	MATERIAL PHOSPHOR BRONZE PER ASTM B-103 ANNEALED	CHK 2-10-93 DA PATTERSON	-	53003-1
FOR APPLICATION TOOLING INFORMATION			WIRE CROSS SECTIONAL AREA RANGE: 0.1-0.41mm ² [202-810] CIR MILS STRANDED	FINISH TIN PLATE 0.00254[.000100] MIN THK PER ASTM B545	APPD 2-10-93 DE MILLER	HEAT TREAT	PART NO
FOR ORDER ENTRY			THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		APPD 2-10-93 JL MECKLEY	AMP AMP Incorporated Harrisburg, PA 17105-3608	
PRODUCT INFORMATION CENTER 1-800-522-6752					PRODUCT SPEC -	NAME TERMINAL, SHORT SPRING SPADE, BUDGET	
TOOLING ASSISTANCE CENTER 1-800-722-1111					APPLICATION SPEC -	SIZE C	CAGE CODE 00779
1-800-526-5142					WEIGHT -	DRAWING NO C= 53003	
						SCALE 10:1	SHEET 10F 1