




## Features

- High resistance to heat and humidity
- Resistance to mechanical shock and pressure
- Accurate dimensions for automatic surface mounting
- Wide inductance range (1.0 nH to 1000  $\mu$ H)
- RoHS compliant\*



The CM10 & CM16 series are currently available but not recommended for new designs. The **C100505**, **C160808**, **CW100505** and **CW160808** are possible alternatives.

## CM45, CM16, CM10 SMT Chip Inductors

### General Specifications


|                              |                   |
|------------------------------|-------------------|
| Temperature Rise             |                   |
| CM10, CM16, CM45             | 20 °C max.        |
| Ambient Temperature          |                   |
| CM10, CM16                   | 80 °C max.        |
| CM45                         | 100 °C max.       |
| Operating Temperature        |                   |
| CM10, CM16                   | -40 °C to +100 °C |
| CM45                         | -40 °C to +125 °C |
| Storage Temperature          |                   |
| CM10, CM16                   | -40 °C to +100 °C |
| CM45                         | -40 °C to +125 °C |
| Resistance to Soldering Heat | 260 °C, 5 seconds |

### Materials


|               |                 |
|---------------|-----------------|
| Core Material |                 |
| CM10, CM16    | Alumina ceramic |
| CM45          | Ferrite Core    |
| Coil Type     |                 |
| CM10, CM16    | Copper plating  |
| CM45          | Copper wire     |
| Enclosure     |                 |
| CM10, CM16    | Resin           |
| CM45          | Epoxy resin     |
| Terminal      | Sn              |

### Product Dimensions

#### CM100505, CM160808




#### CM453232



DIMENSIONS:  $\frac{\text{MM}}{\text{(INCHES)}}$

### Recommended Land Pattern Dimensions



| Series | a                         | b                         | c                         |
|--------|---------------------------|---------------------------|---------------------------|
| CM10   | 0.5 to 0.6 (.019 to .023) | 1.5 to 1.7 (.059 to .067) | 0.5 to 0.6 (.019 to .023) |
| CM16   | 0.8 to 1.0 (.032 to .039) | 2.0 to 2.6 (.079 to .102) | 0.7 to 0.9 (.028 to .035) |
| CM45   | 2.0 to 2.4 (.079 to .094) | 5.0 to 5.3 (.197 to .209) | 1.4 to 1.7 (.055 to .067) |

\*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.


Users should verify actual device performance in their specific applications.

# CM45, CM16, CM10 SMT Chip Inductors


**BOURNS®**

## Packaging Specifications


**CM100505**



**CM160808**



**CM453232**



DIMENSIONS:  $\frac{\text{MM}}{(\text{INCHES})}$


| Series | A           | B           | W            | F           | E           | P1          | P2          | P3          | D0 Dia.     | D1 Dia.     | t1          | t2          |
|--------|-------------|-------------|--------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|
| CM10   | 0.71 (.027) | 1.21 (.047) | 8.00 (.315)  | 3.50 (.138) | 1.75 (.069) | 4.00 (.157) | 2.00 (.079) | 4.00 (.157) | 1.50 (.059) | --          | --          | 0.66 (.026) |
| CM16   | 1.00 (.039) | 1.80 (.071) | 8.00 (.315)  | 3.50 (.138) | 1.75 (.069) | 4.00 (.157) | 2.00 (.079) | 4.00 (.157) | 1.50 (.059) | 0.60 (.024) | 0.27 (.011) | 1.20 (.047) |
| CM45   | 3.60 (.142) | 4.90 (.193) | 12.00 (.472) | 5.50 (.217) | 1.75 (.069) | 8.00 (.315) | 2.00 (.079) | 4.00 (.157) | 1.50 (.059) | 1.00 (.039) | 0.25 (.010) | 3.50 (.138) |

## Reel Dimensions

| Series     | A           | B       | C         | D         | E        | W         |
|------------|-------------|---------|-----------|-----------|----------|-----------|
| CM10, CM16 | 178 (7.008) | 60 min. | 13 (.512) | 21 (.827) | 2 (.079) | 9 (.354)  |
| CM45       |             |         |           |           |          | 13 (.512) |

## Packaging

| Series | Quantity    | Weight |
|--------|-------------|--------|
| CM10   | 10,000 pcs. | 150 g  |
| CM16   | 3,000 pcs.  | 90 g   |
| CM45   | 500 pcs.    | 100 g  |




Specifications are subject to change without notice.  
The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.  
Users should verify actual device performance in their specific applications.

## CM45, CM16, CM10 SMT Chip Inductors


**BOURNS®**

### Soldering Profiles

#### CM100505, CM160808



#### CM453232



Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

# CM45, CM16, CM10 SMT Chip Inductors

**BOURNS®**

| RoHS Compliant<br>0402 Size<br>Part Number | Inductance<br>nH | Tolerance | Q<br>min. | Test Frequency<br>MHz | SRF min.<br>MHz | RDC<br>ohm max | IDC<br>mA max |
|--------------------------------------------|------------------|-----------|-----------|-----------------------|-----------------|----------------|---------------|
| CM100505-1N0DL                             | 1.00             | ±0.3 nH   | 8         | 100                   | 6000            | 0.05           | 400           |
| CM100505-1N2DL                             | 1.20             | ±0.3 nH   | 8         | 100                   | 6000            | 0.06           | 400           |
| CM100505-1N5DL                             | 1.50             | ±0.3 nH   | 8         | 100                   | 6000            | 0.07           | 400           |
| CM100505-1N8DL                             | 1.80             | ±0.3 nH   | 8         | 100                   | 6000            | 0.08           | 400           |
| CM100505-2N2DL                             | 2.20             | ±0.3 nH   | 8         | 100                   | 6000            | 0.09           | 400           |
| CM100505-2N7DL                             | 2.70             | ±0.3 nH   | 8         | 100                   | 5500            | 0.10           | 400           |
| CM100505-3N3DL                             | 3.30             | ±0.3 nH   | 8         | 100                   | 5500            | 0.12           | 400           |
| CM100505-3N9DL                             | 3.90             | ±0.3 nH   | 8         | 100                   | 5200            | 0.15           | 360           |
| CM100505-4N7DL                             | 4.70             | ±0.3 nH   | 8         | 100                   | 4800            | 0.17           | 360           |
| CM100505-5N6DL                             | 5.60             | ±0.3 nH   | 8         | 100                   | 4600            | 0.19           | 340           |
| CM100505-6N8JL                             | 6.80             | ± 5 %     | 8         | 100                   | 4000            | 0.30           | 320           |
| CM100505-8N2JL                             | 8.20             | ± 5 %     | 8         | 100                   | 3500            | 0.35           | 320           |
| CM100505-10NJL                             | 10.00            | ± 5 %     | 8         | 100                   | 2800            | 0.41           | 320           |
| CM100505-12NJL                             | 12.00            | ± 5 %     | 8         | 100                   | 2800            | 0.45           | 320           |
| CM100505-15NJL                             | 15.00            | ± 5 %     | 8         | 100                   | 2500            | 0.60           | 240           |
| CM100505-18NJL                             | 18.00            | ± 5 %     | 8         | 100                   | 2200            | 0.70           | 240           |
| CM100505-22NJL                             | 22.00            | ± 5 %     | 8         | 100                   | 2000            | 0.80           | 200           |
| CM100505-27NJL                             | 27.00            | ± 5 %     | 8         | 100                   | 1800            | 1.2            | 200           |
| CM100505-33NJL                             | 33.00            | ± 5 %     | 8         | 100                   | 1800            | 1.4            | 170           |
| CM100505-39NJL                             | 39.00            | ± 5 %     | 8         | 100                   | 1800            | 1.7            | 150           |
| CM100505-47NJL                             | 47.00            | ± 5 %     | 8         | 100                   | 1800            | 2.1            | 140           |
| CM100505-56NJL                             | 56.00            | ± 5 %     | 8         | 100                   | 1500            | 2.5            | 130           |
| CM100505-68NJL                             | 68.00            | ± 5 %     | 8         | 100                   | 1500            | 4.0            | 120           |
| CM100505-82NJL                             | 82.00            | ± 5 %     | 8         | 100                   | 1400            | 4.5            | 110           |
| CM100505-R10JL                             | 100.00           | ± 5 %     | 8         | 100                   | 1200            | 5.5            | 90            |

Specifications are subject to change without notice.  
The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.  
Users should verify actual device performance in their specific applications.

# CM45, CM16, CM10 SMT Chip Inductors

**BOURNS®**

| RoHS Compliant<br>0603 Size<br>Part Number | Inductance<br>nH | Tolerance | Q<br>min. | Test Frequency<br>MHz | SRF min.<br>MHz | RDC<br>ohm max | IDC<br>mA max |
|--------------------------------------------|------------------|-----------|-----------|-----------------------|-----------------|----------------|---------------|
| CM160808-1N5DL                             | 1.5              | ± 0.3 nH  | 8         | 100                   | 6000            | 0.07           | 500           |
| CM160808-1N8DL                             | 1.8              | ± 0.3 nH  | 8         | 100                   | 6000            | 0.08           | 500           |
| CM160808-2N2DL                             | 2.2              | ± 0.3 nH  | 8         | 100                   | 6000            | 0.09           | 500           |
| CM160808-2N7DL                             | 2.7              | ± 0.3 nH  | 8         | 100                   | 6000            | 0.10           | 500           |
| CM160808-3N3DL                             | 3.3              | ± 0.3 nH  | 9         | 100                   | 5500            | 0.12           | 500           |
| CM160808-3N9JL                             | 3.9              | ±5 %      | 9         | 100                   | 5500            | 0.15           | 450           |
| CM160808-4N7JL                             | 4.7              | ±5 %      | 9         | 100                   | 4800            | 0.17           | 450           |
| CM160808-5N6JL                             | 5.6              | ±5 %      | 9         | 100                   | 4600            | 0.18           | 430           |
| CM160808-6N8JL                             | 6.8              | ±5 %      | 9         | 100                   | 3550            | 0.20           | 430           |
| CM160808-8N2JL                             | 8.2              | ±5 %      | 9         | 100                   | 3500            | 0.28           | 400           |
| CM160808-10NJL                             | 10               | ±5 %      | 10        | 100                   | 2800            | 0.32           | 400           |
| CM160808-12NJL                             | 12               | ±5 %      | 10        | 100                   | 2800            | 0.35           | 400           |
| CM160808-15NJL                             | 15               | ±5 %      | 10        | 100                   | 2500            | 0.41           | 350           |
| CM160808-18NJL                             | 18               | ±5 %      | 10        | 100                   | 2300            | 0.45           | 350           |
| CM160808-22NJL                             | 22               | ±5 %      | 10        | 100                   | 2000            | 0.50           | 300           |
| CM160808-27NJL                             | 27               | ±5 %      | 10        | 100                   | 2000            | 0.55           | 300           |
| CM160808-33NJL                             | 33               | ±5 %      | 10        | 100                   | 1800            | 0.60           | 300           |
| CM160808-39NJL                             | 39               | ±5 %      | 11        | 100                   | 1800            | 0.80           | 300           |
| CM160808-47NJL                             | 47               | ±5 %      | 11        | 100                   | 1800            | 0.95           | 250           |
| CM160808-56NJL                             | 56               | ±5 %      | 12        | 100                   | 1800            | 1.2            | 250           |
| CM160808-68NJL                             | 68               | ±5 %      | 12        | 100                   | 1500            | 1.3            | 250           |
| CM160808-82NJL                             | 82               | ±5 %      | 12        | 100                   | 1500            | 1.5            | 250           |
| CM160808-R10JL                             | 100              | ±5 %      | 12        | 100                   | 1300            | 1.8            | 200           |
| CM160808-R12JL                             | 120              | ±5 %      | 5         | 25.2                  | 1200            | 3.0            | 130           |
| CM160808-R15JL                             | 150              | ±5 %      | 5         | 25.2                  | 1100            | 4.5            | 100           |
| CM160808-R18JL                             | 180              | ±5 %      | 4         | 25.2                  | 1000            | 6.5            | 80            |
| CM160808-R22JL                             | 220              | ±5 %      | 4         | 25.2                  | 900             | 7.5            | 70            |

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

# CM45, CM16, CM10 SMT Chip Inductors

**BOURNS®**

| RoHS Compliant<br>1812 Size<br>Part Number | Inductance<br>μH | Std.<br>Tolerance | Std. Tol.<br>Code | 1/2<br>Tolerance | 1/2 Tol.<br>Code | Q<br>min. | Test Freq.<br>MHz | SRF min.<br>MHz | RDC<br>ohm max | IDC<br>mA max |
|--------------------------------------------|------------------|-------------------|-------------------|------------------|------------------|-----------|-------------------|-----------------|----------------|---------------|
| CM453232-R10<1>L                           | 0.10             | ±20 %             | M                 | ±10 %            | K                | 35        | 25.2              | 300             | 0.18           | 800           |
| CM453232-R12<1>L                           | 0.12             | ±20 %             | M                 | ±10 %            | K                | 35        | 25.2              | 280             | 0.2            | 770           |
| CM453232-R15<1>L                           | 0.15             | ±20 %             | M                 | ±10 %            | K                | 35        | 25.2              | 250             | 0.22           | 730           |
| CM453232-R18<1>L                           | 0.18             | ±20 %             | M                 | ±10 %            | K                | 35        | 25.2              | 220             | 0.24           | 700           |
| CM453232-R22<1>L                           | 0.22             | ±20 %             | M                 | ±10 %            | K                | 40        | 25.2              | 200             | 0.25           | 665           |
| CM453232-R27<1>L                           | 0.27             | ±20 %             | M                 | ±10 %            | K                | 40        | 25.2              | 180             | 0.26           | 635           |
| CM453232-R33<1>L                           | 0.33             | ±20 %             | M                 | ±10 %            | K                | 40        | 25.2              | 165             | 0.28           | 605           |
| CM453232-R39<1>L                           | 0.39             | ±20 %             | M                 | ±10 %            | K                | 40        | 25.2              | 150             | 0.30           | 575           |
| CM453232-R47<1>L                           | 0.47             | ±20 %             | M                 | ±10 %            | K                | 40        | 25.2              | 145             | 0.32           | 545           |
| CM453232-R56<1>L                           | 0.56             | ±20 %             | M                 | ±10 %            | K                | 40        | 25.2              | 140             | 0.36           | 520           |
| CM453232-R68<1>L                           | 0.68             | ±20 %             | M                 | ±10 %            | K                | 40        | 25.2              | 135             | 0.40           | 500           |
| CM453232-R82<1>L                           | 0.82             | ±20 %             | M                 | ±10 %            | K                | 40        | 25.2              | 130             | 0.45           | 475           |
| CM453232-1R0<1>L                           | 1.0              | ±10 %             | K                 | ±5 %             | J                | 50        | 7.96              | 100             | 0.50           | 450           |
| CM453232-1R2<1>L                           | 1.2              | ±10 %             | K                 | ±5 %             | J                | 50        | 7.96              | 80              | 0.55           | 430           |
| CM453232-1R5<1>L                           | 1.5              | ±10 %             | K                 | ±5 %             | J                | 50        | 7.96              | 70              | 0.60           | 410           |
| CM453232-1R8<1>L                           | 1.8              | ±10 %             | K                 | ±5 %             | J                | 50        | 7.96              | 60              | 0.65           | 390           |
| CM453232-2R2<1>L                           | 2.2              | ±10 %             | K                 | ±5 %             | J                | 50        | 7.96              | 55              | 0.70           | 380           |
| CM453232-2R7<1>L                           | 2.7              | ±10 %             | K                 | ±5 %             | J                | 50        | 7.96              | 50              | 0.75           | 370           |
| CM453232-3R3<1>L                           | 3.3              | ±10 %             | K                 | ±5 %             | J                | 50        | 7.96              | 45              | 0.80           | 355           |
| CM453232-3R9<1>L                           | 3.9              | ±10 %             | K                 | ±5 %             | J                | 50        | 7.96              | 40              | 0.90           | 330           |
| CM453232-4R7<1>L                           | 4.7              | ±10 %             | K                 | ±5 %             | J                | 50        | 7.96              | 35              | 1.00           | 315           |
| CM453232-5R6<1>L                           | 5.6              | ±10 %             | K                 | ±5 %             | J                | 50        | 7.96              | 33              | 1.10           | 300           |
| CM453232-6R8<1>L                           | 6.8              | ±10 %             | K                 | ±5 %             | J                | 50        | 7.96              | 27              | 1.2            | 285           |
| CM453232-8R2<1>L                           | 8.2              | ±10 %             | K                 | ±5 %             | J                | 50        | 7.96              | 25              | 1.4            | 270           |
| CM453232-100<1>L                           | 10               | ±10 %             | K                 | ±5 %             | J                | 50        | 2.52              | 20              | 1.6            | 250           |
| CM453232-120<1>L                           | 12               | ±10 %             | K                 | ±5 %             | J                | 50        | 2.52              | 18              | 2              | 225           |
| CM453232-150<1>L                           | 15               | ±10 %             | K                 | ±5 %             | J                | 50        | 2.52              | 17              | 2.5            | 200           |
| CM453232-180<1>L                           | 18               | ±10 %             | K                 | ±5 %             | J                | 50        | 2.52              | 15              | 2.8            | 190           |
| CM453232-220<1>L                           | 22               | ±10 %             | K                 | ±5 %             | J                | 50        | 2.52              | 13              | 3.2            | 180           |
| CM453232-270<1>L                           | 27               | ±10 %             | K                 | ±5 %             | J                | 50        | 2.52              | 12              | 3.6            | 170           |
| CM453232-330<1>L                           | 33               | ±10 %             | K                 | ±5 %             | J                | 50        | 2.52              | 11              | 4              | 160           |
| CM453232-390<1>L                           | 39               | ±10 %             | K                 | ±5 %             | J                | 50        | 2.52              | 10              | 4.5            | 150           |
| CM453232-470<1>L                           | 47               | ±10 %             | K                 | ±5 %             | J                | 50        | 2.52              | 10              | 5              | 140           |
| CM453232-560<1>L                           | 56               | ±10 %             | K                 | ±5 %             | J                | 50        | 2.52              | 9               | 5.5            | 135           |
| CM453232-680<1>L                           | 68               | ±10 %             | K                 | ±5 %             | J                | 50        | 2.52              | 9               | 6              | 130           |
| CM453232-820<1>L                           | 82               | ±10 %             | K                 | ±5 %             | J                | 50        | 2.52              | 8               | 7              | 120           |
| CM453232-101<1>L                           | 100              | ±10 %             | K                 | ±5 %             | J                | 40        | 2.52              | 8               | 8              | 110           |
| CM453232-121<1>L                           | 120              | ±10 %             | K                 | ±5 %             | J                | 40        | 0.796             | 6               | 8              | 110           |
| CM453232-151<1>L                           | 150              | ±10 %             | K                 | ±5 %             | J                | 40        | 0.796             | 5               | 9              | 105           |
| CM453232-181<1>L                           | 180              | ±10 %             | K                 | ±5 %             | J                | 40        | 0.796             | 5               | 9.5            | 102           |
| CM453232-221<1>L                           | 220              | ±10 %             | K                 | ±5 %             | J                | 40        | 0.796             | 4               | 10             | 100           |
| CM453232-271<1>L                           | 270              | ±10 %             | K                 | ±5 %             | J                | 40        | 0.796             | 4               | 12             | 92            |
| CM453232-331<1>L                           | 330              | ±10 %             | K                 | ±5 %             | J                | 40        | 0.796             | 3.5             | 14             | 85            |
| CM453232-391<1>L                           | 390              | ±10 %             | K                 | ±5 %             | J                | 40        | 0.796             | 3               | 18             | 80            |
| CM453232-471<1>L                           | 470              | ±10 %             | K                 | ±5 %             | J                | 40        | 0.796             | 3               | 26             | 62            |
| CM453232-561<1>L                           | 560              | ±10 %             | K                 | ±5 %             | J                | 30        | 0.796             | 3               | 30             | 50            |
| CM453232-681<1>L                           | 680              | ±10 %             | K                 | ±5 %             | J                | 30        | 0.796             | 3               | 30             | 50            |
| CM453232-821<1>L                           | 820              | ±10 %             | K                 | ±5 %             | J                | 30        | 0.796             | 2.5             | 35             | 30            |
| CM453232-102<1>L                           | 1000             | ±10 %             | K                 | ±5 %             | J                | 30        | 0.252             | 2.5             | 40             | 30            |

<1> Enter tolerance code from standard or 1/2 tolerance column. Example: CM453232-1R2KL is standard tolerance; CM453232-1R2JL is 1/2 tolerance.

REV. 07/15

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.

Users should verify actual device performance in their specific applications.