




PART NUMBER	MATERIAL	"B" HEIGHT +/- .062	IMPRINT AREA "C" +/- .062	VERTICAL REPEAT "D" +/- .062	LABELS PER ROW	STANDARD PKG. QTY.
S100X075VA1Y	GMV16	0.75 [19.0]	0.25 [6.35]	1.00 [25.4]	4	2500
S100X125VA1Y	GMV16	1.25 [31.8]	0.38 [9.53]	1.50 [38.1]	4	2500
S100X150VA1Y	GMV16	1.50 [38.1]	0.50 [12.7]	1.80 [45.7]	4	2500
S100X225VA1Y	GMV16	2.25 [57.2]	0.75 [19.0]	2.50 [63.5]	4	1500
S100X250VA1Y	GMV16	2.50 [63.5]	1.00 [25.4]	2.75 [69.8]	4	1500
S100X400VA1Y	GMV16	4.00 [101.6]	1.00 [25.4]	4.25 [108.0]	4	1000
S100X650VA1Y	GMV16	6.50 [165.1]	1.50 [38.1]	6.75 [171.4]	4	250

NOTES:

1. MILLIMETERS ARE IN [].



										CAD FILENAME/LAYERS		100472BS_DC_C10194/05E	
										PANDUIT CORP. TINLEY PARK, ILLINOIS			
										CUSTOMER DRAWING OPTIMUM SELF-LAM. S100X***VA1Y THERMAL TRANSFER PRINTABLE LABELS			
4	2/25/09	RVU		OBSOLETE PARTS: S***X***VA1, AND S***X***TA1. UPDATE TOLERANCE WITH +/- .062.			5682	R					
3	6/13/08	RVU		VOID			5464	R					
2	5/25/07	RVU		ADDED NEW P/N, S100X225VA1Y.			5021	R					
1	1-8-07	RVU		REVISED TOLERANCE.			4830	R					
0	9-11-06	RVU		DRAWING RELEASED.			4671	R					
REV	DATE	BY	CHK	DESCRIPTION			ECN	-	R	CUST	SUP		

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XX) ± .062			UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY RVU	MAT'L;		SCALE NTS	
DATE 9-22-04	SEE TABLE		DRAWING NO. C10194	
CHK'D		DWG A SIZE		