




Left Side

Connector(s): MPO (No Pins)
 Mode: MM
 Housing Color: Black
 Geom. Spec: N/A

Right Side

Connector(s): MPO (No Pins)
 Mode: MM
 Housing Color: Black
 Geom. Spec: N/A

Notes:

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 A copy of test data will be placed inside or with the unit package.
- 3 Label 2 will not be present on any cable assembly less than 5 meters long.
- 4 The cable meets or exceeds the requirements of GR-409-CORE for both RISER and PLENUM applications.
- 5 The cable meets or exceeds the UL requirements for both RISER and PLENUM applications.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
 CE
 DIST
 16

Rev Per	EC#	MINOR REVISION	DATE	DN	APVD
A2			2/23/2009	-	JB
P	LTR	REVISION RECORD	DATE	DN	APVD

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
meters	
1 P.L.C.	± .005
2 P.L.C.	± .005
3 P.L.C.	± .005
4 P.L.C.	± .005

Restricted To:


DN	Cable Assy Configurator	MATERIAL	HEAT TREAT
OK	James Barry		
APVD	James Barry		
NAME	FO C/A - 24 fiber, XG - 50/125, OFNR-OFNP, MPO (No Pins) to MPO (No Pins)		
SCALE	NTS	SIZE	A2
DRAWING NO	C- 6754687	SHEET	1 of 5
REV	A2		

THIS DRAWING IS A CONTROLLED DOCUMENT.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.


LOC
CE
DIST
16

CAC Customer Layout Rev: D



Pairs Flipped

A-A Fiber Color	Connector Position #	B-B Fiber Color
Blue	1	Orange
Orange	2	Blue
Green	3	Brown
Brown	4	Green
Slate	5	White
White	6	Slate
Red	7	Black
Black	8	Red
Yellow	9	Violet
Violet	10	Yellow
Rose	11	Aqua
Aqua	12	Rose



Lightray Connector Fiber Path

Leg 1 ——— 1 Leg
Leg 2 ——— 2 Leg

DIMENSIONS: meters		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
Ø	1 P.L.C. ± .	Ø	1 P.L.C. ± .
Ø	2 P.L.C. ± .	Ø	2 P.L.C. ± .
Ø	3 P.L.C. ± .	Ø	3 P.L.C. ± .
Ø	4 P.L.C. ± .	Ø	4 P.L.C. ± .

DIN	Cable Assy Configurator	MATERIAL	HEAT TREAT
OK	James Barry		
APVD	James Barry	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608	
NAME: FO C/A - 24 fiber, XG - 50/125, OFNR-OFNP, MPO (No Pins) to MPO (No Pins)			
SCALE	SIZE	DRAWING NO	SHEET
NTS	A2	C- 6754687	2 of 5
REV		A2	

Restricted To:

8 7 6 5 4 3 2 1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Part #	L (meters)	L (feet)	MPO (No Pins), Black		MPO (No Pins), Black	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-6754687-1	3.048 - 3.353	10.00 - 11.00	0.75	-	0.75	-
0-6754687-2	6.096 - 6.706	20.00 - 22.00	0.76	-	0.76	-
0-6754687-3	9.144 - 9.754	30.00 - 32.00	0.76	-	0.76	-
0-6754687-4	12.192 - 12.802	40.00 - 42.00	0.77	-	0.77	-
0-6754687-5	15.240 - 15.850	50.00 - 52.00	0.77	-	0.77	-
0-6754687-6	18.288 - 18.898	60.00 - 62.00	0.78	-	0.78	-
0-6754687-7	21.336 - 21.946	70.00 - 72.00	0.78	-	0.78	-
0-6754687-8	24.384 - 24.994	80.00 - 82.00	0.79	-	0.79	-
0-6754687-9	27.432 - 28.042	90.00 - 92.00	0.79	-	0.79	-
1-6754687-0	30.480 - 31.394	100.00 - 103.00	0.8	-	0.8	-
1-6754687-1	33.528 - 34.442	110.00 - 113.00	0.8	-	0.8	-
1-6754687-2	36.576 - 37.490	120.00 - 123.00	0.8	-	0.8	-
1-6754687-3	39.624 - 40.538	130.00 - 133.00	0.81	-	0.81	-
1-6754687-4	42.672 - 43.586	140.00 - 143.00	0.81	-	0.81	-
1-6754687-5	45.720 - 46.634	150.00 - 153.00	0.82	-	0.82	-
1-6754687-6	48.768 - 49.682	160.00 - 163.00	0.82	-	0.82	-
1-6754687-7	51.816 - 52.730	170.00 - 173.00	0.83	-	0.83	-
1-6754687-8	54.864 - 55.778	180.00 - 183.00	0.83	-	0.83	-
1-6754687-9	57.912 - 58.826	190.00 - 193.00	0.84	-	0.84	-
2-6754687-0	60.960 - 62.179	200.00 - 204.00	0.84	-	0.84	-
2-6754687-1	64.008 - 65.227	210.00 - 214.00	0.85	-	0.85	-
2-6754687-2	67.056 - 68.275	220.00 - 224.00	0.85	-	0.85	-
2-6754687-3	70.104 - 71.323	230.00 - 234.00	0.86	-	0.86	-
2-6754687-4	73.152 - 74.371	240.00 - 244.00	0.86	-	0.86	-
2-6754687-5	76.200 - 77.419	250.00 - 254.00	0.86	-	0.86	-
2-6754687-6	79.248 - 80.467	260.00 - 264.00	0.87	-	0.87	-
2-6754687-7	82.296 - 83.515	270.00 - 274.00	0.87	-	0.87	-
2-6754687-8	85.344 - 86.563	280.00 - 284.00	0.88	-	0.88	-
2-6754687-9	88.392 - 89.611	290.00 - 294.00	0.88	-	0.88	-
3-6754687-0	91.440 - 93.269	300.00 - 306.00	0.89	-	0.89	-
3-6754687-1	94.488 - 96.378	310.00 - 316.20	0.89	-	0.89	-
3-6754687-2	97.536 - 99.487	320.00 - 326.40	0.9	-	0.9	-
3-6754687-3	100.584 - 102.596	330.00 - 336.60	0.9	-	0.9	-
3-6754687-4	103.632 - 105.705	340.00 - 346.80	0.91	-	0.91	-
3-6754687-5	106.680 - 108.814	350.00 - 357.00	0.91	-	0.91	-
3-6754687-6	109.728 - 111.923	360.00 - 367.20	0.91	-	0.91	-
3-6754687-7	112.776 - 115.032	370.00 - 377.40	0.92	-	0.92	-
3-6754687-8	115.824 - 118.140	380.00 - 387.60	0.92	-	0.92	-
3-6754687-9	118.872 - 121.249	390.00 - 397.80	0.93	-	0.93	-
4-6754687-0	121.920 - 124.358	400.00 - 408.00	0.93	-	0.93	-
4-6754687-1	124.968 - 127.467	410.00 - 418.20	0.94	-	0.94	-
4-6754687-2	128.016 - 130.576	420.00 - 428.40	0.94	-	0.94	-
4-6754687-3	131.064 - 133.685	430.00 - 438.60	0.95	-	0.95	-
4-6754687-4	134.112 - 136.794	440.00 - 448.80	0.95	-	0.95	-

Qty	U of M	Description	Item No.
0.167	piece	Label, 1 & 2	23
3	piece	Trace Label	22
4	piece	Ferrule, MT, MM, 12 Fiber	21
0.2	RL	Electrical Tape	20
4.06	meters	Oval Tube, Aqua	19
4	piece	Boot, MPO - Black	18
4	piece	Dust Cover	17
1	piece	Braided Sleeve	16
1	piece	Caution Label	15
1	piece	Pulling Sock	14
4	piece	Spirap 5.5"	13
1	piece	Heat Shrink Tubing	12
0.5	piece	Foam Cap	11
4	piece	Construction tape	10
2	piece	Heat Shrink Tubing	9
4	piece	Crimp Ring	8
4	piece	Spring Retainer	7
4	piece	Spring	6
4	piece	Connector Housing	5
AR	meter	24 Fiber, XG-50/125, 7.8mm, CLT, Aqua, OFNR/OFNP	4
2	piece	VACUUM HOSE, SPIRAFLEX 1 FOOT	3
4	piece	Pin Holder w/out Pins	2
4	piece	Mini boot, 12 fiber	1

	A2	Rev Per EC#	MINOR REVISION	2/23/2009	-
P	LTR	REVISION RECORD		DATE	DIN

DIMENSIONS: meters		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 P.L.C	±
		1 P.L.C	±
		2 P.L.C	±
		3 P.L.C	±
		4 P.L.C	±

Restricted To:

DIN Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK	James Barry			
APVD	James Barry			
NAME FO C/A - 24 fiber, XG - 50/125, OFNR-OFNP, MPO (No Pins) to MPO (No Pins)				
SCALE	SIZE	DRAWING NO	SHEET	REV
NTS	A2	C- 6754687	3 of 5	A2

8 7 6 5 4 3 2 1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.


THIS DRAWING IS A CONTROLLED DOCUMENT.
PAGE NO

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Part #	L (meters)	L (feet)	MPO (No Pins), Black		MPO (No Pins), Black	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
4-6754687-5	137.160 - 139.903	450.00 - 459.00	0.96	-	0.96	-
4-6754687-6	140.208 - 143.012	460.00 - 469.20	0.96	-	0.96	-
4-6754687-7	143.256 - 146.121	470.00 - 479.40	0.96	-	0.96	-
4-6754687-8	146.304 - 149.230	480.00 - 489.60	0.97	-	0.97	-
4-6754687-9	149.352 - 152.339	490.00 - 499.80	0.97	-	0.97	-
5-6754687-0	152.400 - 155.448	500.00 - 510.00	0.98	-	0.98	-
5-6754687-1	160.020 - 163.220	525.00 - 535.50	0.99	-	0.99	-
5-6754687-2	167.640 - 170.993	550.00 - 561.00	1	-	1	-
5-6754687-3	175.260 - 178.765	575.00 - 586.50	1.01	-	1.01	-
5-6754687-4	182.880 - 186.538	600.00 - 612.00	1.02	-	1.02	-
5-6754687-5	190.500 - 194.310	625.00 - 637.50	1.04	-	1.04	-
5-6754687-6	198.120 - 202.082	650.00 - 663.00	1.05	-	1.05	-
5-6754687-7	205.740 - 209.855	675.00 - 688.50	1.06	-	1.06	-
5-6754687-8	213.360 - 217.627	700.00 - 714.00	1.07	-	1.07	-
5-6754687-9	220.980 - 225.400	725.00 - 739.50	1.08	-	1.08	-
6-6754687-0	228.600 - 233.172	750.00 - 765.00	1.09	-	1.09	-
6-6754687-1	236.220 - 240.944	775.00 - 790.50	1.1	-	1.1	-
6-6754687-2	243.840 - 248.717	800.00 - 816.00	1.12	-	1.12	-
6-6754687-3	251.460 - 256.489	825.00 - 841.50	1.13	-	1.13	-
6-6754687-4	259.080 - 264.262	850.00 - 867.00	1.14	-	1.14	-
6-6754687-5	266.700 - 272.034	875.00 - 892.50	1.15	-	1.15	-
6-6754687-6	274.320 - 279.806	900.00 - 918.00	1.16	-	1.16	-
6-6754687-7	281.940 - 287.579	925.00 - 943.50	1.17	-	1.17	-
6-6754687-8	289.560 - 295.351	950.00 - 969.00	1.18	-	1.18	-
6-6754687-9	297.180 - 303.124	975.00 - 994.50	1.2	-	1.2	-
7-6754687-0	304.800 - 310.896	1000.00 - 1020.00	1.21	-	1.21	-
7-6754687-1	4.572 - 4.877	15.00 - 16.00	0.76	-	0.76	-
7-6754687-2	7.620 - 8.230	25.00 - 27.00	0.76	-	0.76	-
7-6754687-3	10.668 - 11.278	35.00 - 37.00	0.77	-	0.77	-
7-6754687-4	13.716 - 14.326	45.00 - 47.00	0.77	-	0.77	-
7-6754687-5	16.764 - 17.374	55.00 - 57.00	0.78	-	0.78	-

	A2	Rev Per EC#	MINOR REVISION	2/23/2009	-	JB	
P	LTR	REVISION RECORD		DATE	DIN	APVD	



TOLERANCES UNLESS OTHERWISE SPECIFIED:	
9 P.L.C.	± .
1 P.L.C.	± .
2 P.L.C.	± .
3 P.L.C.	± .
4 P.L.C.	± .

Restricted To:

DWG Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK	James Barry	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD	James Barry			
NAME FO C/A - 24 fiber, XG - 50/125, OFNR-OFNP, MPO (No Pins) to MPO (No Pins)				
SCALE NTS	SIZE A2	DRAWING NO C- 6754687	SHEET 4 of 5	REV A2

8 7 6 5 4 3 2 1

D
C
B
A

THIS DRAWING IS A CONTROLLED DOCUMENT.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

8

7

6

5

4

3

2

1

Label 1

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1




Trace # - Bar Code

Trace # - Human Readable


Part Number

Country of Origin


This label is used on all lengths on this drawing.



Protective Cover
Bottom End



Pulling Sock
Top End



DIMENSIONS:
meters

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

Restricted To:

DWG Cable Assy Configurator		MATERIAL -	HEAT TREAT -	
CHK James Barry		AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD James Barry				
NAME FO C/A - 24 fiber, XG - 50/125, OFNR-OFNP, MPO (No Pins) to MPO (No Pins)				
SCALE NTS	SIZE A2	DRAWING NO C- 6754687		SHEET 5 of 5
				REV A2