


Silicon NPN epitaxial planer transistor

■ Features


- Costs can be reduced through downsizing of the equipment and reduction of the number of parts.
- MT-1 type package, allowing supply with the radial taping.

■ Resistance by Part Number

	(R ₁)	(R ₂)
● UNR6211	10kΩ	10kΩ
● UNR6212	22kΩ	22kΩ
● UNR6213	47kΩ	47kΩ
● UNR6214	10kΩ	47kΩ
● UNR6215	10kΩ	—
● UNR6216	4.7kΩ	—
● UNR6217	22kΩ	—
● UNR6218	0.51kΩ	5.1kΩ
● UNR6219	1kΩ	10kΩ
● UNR6210	47kΩ	—
● UNR621D	47kΩ	10kΩ
● UNR621E	47kΩ	22kΩ
● UNR621F	4.7kΩ	10kΩ
● UNR621K	10kΩ	4.7kΩ
● UNR621L	4.7kΩ	4.7kΩ



Internal Connection



■ Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Ratings	Unit
Collector to base voltage	V_{CBO}	50	V
Collector to emitter voltage	V_{CEO}	50	V
Collector current	I_C	100	mA
Total power dissipation	P_T	400	mW
Junction temperature	T_j	150	°C
Storage temperature	T_{stg}	-55 to +150	°C

Note) The Part numbers in the Parenthesis show conventional part number.

**UNR6211/6212/6213/6214/6215/6216/6217/6218/
Transistors with built-in Resistor 6219/6210/621D/621E/621F/621K/621L**


Electrical Characteristics (Ta=25°C)

Parameter		Symbol	Conditions	min	typ	max	Unit
Collector cutoff current		I _{CBO}	V _{CB} = 50V, I _E = 0			0.1	μA
		I _{CEO}	V _{CE} = 50V, I _B = 0			0.5	μA
Emitter cutoff current	UNR6211	I _{EBO}	V _{EB} = 6V, I _C = 0			0.5	mA
	UNR6212/6214/621E/621D					0.2	
	UNR6213					0.1	
	UNR6215/6216/6217/6210					0.01	
	UNR621F/621K					1.0	
	UNR6219					1.5	
	UNR6218/621L					2.0	
Collector to base voltage		V _{CBO}	I _C = 10μA, I _E = 0	50			V
Collector to emitter voltage		V _{CEO}	I _C = 2mA, I _B = 0	50			V
Forward current transfer ratio	UNR6211	h _{FE}	V _{CE} = 10V, I _C = 5mA	35			
	UNR6212/621E			60			
	UNR6213/6214			80			
	UNR6215*/6216*/6217*/6210*			160		460	
	UNR621F/621D/6219			30			
	UNR6218/621K/621L			20			
Collector to emitter saturation voltage		V _{CE(sat)}	I _C = 10mA, I _B = 0.3mA			0.25	V
Output voltage high level		V _{OH}	V _{CC} = 5V, V _B = 0.5V, R _L = 1kΩ	4.9			V
Output voltage low level		V _{OL}	V _{CC} = 5V, V _B = 2.5V, R _L = 1kΩ			0.2	V
			V _{OC} = 5V, V _B = 3.5V, R ₁ = 1kΩ			0.2	
			V _{CC} = 5V, V _B = 10V, R ₁ = 1kΩ			0.2	
			V _{CC} = 5V, V _B = 6V, R _L = 1kΩ			0.2	
Transition frequency		f _T	V _{CB} = 10V, I _E = −2mA, f = 200MHz		150		MHz
Input resistance	UNR6211/6214/6215/621K	R _i		(−30%)	10	(±30%)	kΩ
	UNR6212/6217				22		
	UNR6213/621D/621E/6210				47		
	UNR6216/621F/621L				4.7		
	UNR6218				0.51		
	UNR6219				1		
Resistance ratio	UNR6211/6212/6213/621L	R ₁ /R ₂		0.8	1.0	1.2	
	UNR6214			0.17	0.21	0.25	
	UNR6218/6219			0.08	0.1	0.12	
	UNR621D			3.7	4.7	5.7	
	UNR621E			1.7	2.14	2.6	
	UNR621F			0.37	0.47	0.57	
	UNR621K			1.7	2.13	2.6	







* h_{FE} rank classification (UNR6215/6216/6217/6210)

Rank	Q	R	S
h _{FE}	160 to 260	210 to 340	290 to 460


Common characteristics chart




Characteristics charts of UNR6211






Characteristics charts of UNR6212









Characteristics charts of UNR6213







Characteristics charts of UNR6214






Characteristics charts of UNR6215









Characteristics charts of UNR6216







Characteristics charts of UNR6217






Characteristics charts of UNR6218









Characteristics charts of UNR6219














Characteristics charts of UNR6210






Characteristics charts of UNR621D









Characteristics charts of UNR621E







Characteristics charts of UNR621F





Characteristics charts of UNR621K



Characteristics charts of UNR621L





Request for your special attention and precautions in using the technical information and semiconductors described in this material

- (1) An export permit needs to be obtained from the competent authorities of the Japanese Government if any of the products or technologies described in this material and controlled under the "Foreign Exchange and Foreign Trade Law" is to be exported or taken out of Japan.
- (2) The technical information described in this material is limited to showing representative characteristics and applied circuit examples of the products. It does not constitute the warranting of industrial property, the granting of relative rights, or the granting of any license.
- (3) The products described in this material are intended to be used for standard applications or general electronic equipment (such as office equipment, communications equipment, measuring instruments and household appliances).
Consult our sales staff in advance for information on the following applications:
 - Special applications (such as for airplanes, aerospace, automobiles, traffic control equipment, combustion equipment, life support systems and safety devices) in which exceptional quality and reliability are required, or if the failure or malfunction of the products may directly jeopardize life or harm the human body.
 - Any applications other than the standard applications intended.
- (4) The products and product specifications described in this material are subject to change without notice for reasons of modification and/or improvement. At the final stage of your design, purchasing, or use of the products, therefore, ask for the most up-to-date Product Standards in advance to make sure that the latest specifications satisfy your requirements.
- (5) When designing your equipment, comply with the guaranteed values, in particular those of maximum rating, the range of operating power supply voltage and heat radiation characteristics. Otherwise, we will not be liable for any defect which may arise later in your equipment.
Even when the products are used within the guaranteed values, redundant design is recommended, so that such equipment may not violate relevant laws or regulations because of the function of our products.
- (6) When using products for which dry packing is required, observe the conditions (including shelf life and after-unpacking standby time) agreed upon when specification sheets are individually exchanged.
- (7) No part of this material may be reprinted or reproduced by any means without written permission from our company.

Please read the following notes before using the datasheets

- A. These materials are intended as a reference to assist customers with the selection of Panasonic semiconductor products best suited to their applications.
Due to modification or other reasons, any information contained in this material, such as available product types, technical data, and so on, is subject to change without notice.
Customers are advised to contact our semiconductor sales office and obtain the latest information before starting precise technical research and/or purchasing activities.
- B. Panasonic is endeavoring to continually improve the quality and reliability of these materials but there is always the possibility that further rectifications will be required in the future. Therefore, Panasonic will not assume any liability for any damages arising from any errors etc. that may appear in this material.
- C. These materials are solely intended for a customer's individual use.
Therefore, without the prior written approval of Panasonic, any other use such as reproducing, selling, or distributing this material to a third party, via the Internet or in any other way, is prohibited.