

Broadband Solutions

3399147 | 125U(TD)110WP1100TAPE

Toneable ConQuest® Empty Conduit, 1 1/4 in, SDR 11, blue, with pull tape

Dimensions

Nominal Size	1-1/4 in
Wall Thickness Designation	SDR 11
Inner Diameter, nominal	33.985 mm 1.338 in
Length	914.40 m 3000.00 ft
Outer Diameter, nominal	42.164 mm 1.660 in
Wall Thickness, minimum	3.835 mm 0.151 in
Weight	320.0 lb/kft

General Specifications

Color	Blue
Conduit Type	Toneable
Wall Type	Smooth
Brand	ConQuest®
Warranty	One year

Material Specifications

Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm ³
Density, minimum	0.941 g/cm ³
Design Standard	ASTM D3350-05
Environmental Stress Crack Resistance	Failure rate of 10% within 96 hours
Environmental Stress Test Method	ASTM D1693, ESCR Condition B
Flexural Modulus, minimum	552 N/mm ² 80000 psi
Flexural Property Test Method	ASTM D790
Hydrostatic Design Basis	Not pressure rated
Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE)
Melt Flow Rate Test Method	ASTM D1238
Melt Flow Rate, maximum	0.39 g/10 min
Tensile Property Test Method	ASTM D638
Tensile Strength at yield, minimum	21 N/mm ² 3000 psi

Mechanical Specifications

Minimum Bend Radius, unsupported	457.2 mm 18.0 in
----------------------------------	--------------------

3399147 | 125U(TD)110WP1100TAPE

Pulling Tension, maximum	689.5 kg 1520.0 lb
Pulling Tension Note	Applies to products manufactured after December 31, 2012

Pull Line Specifications

Breaking Strength	499.0 kg 1100.0 lb
Material Type	Polyester
Pull Line Type	Tape

Tone Wire Specifications

Conductor Diameter	1.0236 mm 0.0403 in
Conductor Elongation, maximum	1 %
Conductor Gauge	18 AWG
Conductor Resistance	26.7 ohms/kft
Conductor Tensile Strength, minimum	827 N/mm ² 120000 psi
Conductor Type	Solid
Insulation Dielectric Strength	3200 V/mil
Insulation Elongation, minimum	250 %
Insulation Material Type	Fluoropolymer coated copper-clad steel wire
Insulation Tensile Strength, minimum	21 N/mm ² 3000 psi
Insulation Thickness, nominal	0.203 mm 0.008 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance