


Well known for their quality and reliability, **Bulgin's toggle switches** are **cost effective** solutions to many existing applications. These switches offer features at an attractive price point often well below that of the existing competition.

- ⬢ Nylon and Metal switch variants
- ⬢ Multiple Lever Options
- ⬢ Ratings up to 20A, 250V ac - 277V ac
- ⬢ IP67 panel seal versions, supplied complete with gaskets (3900 Series – All Variants)
- ⬢ Single and double pole
- ⬢ Choice of circuit options including 3 position and momentary
- ⬢ Mounting hole: 12.7mm diameter.
- ⬢ Sealing accessories available
- ⬢ Quick Connect, Solder, Screw and PCB Termination Options






































3900 Metal Toggle Switches

16A 250Vac - IP67 Sealed Versions



Key Features

- Metal toggle switches
- Ratings up to 20A, 277V ac
- Single and double pole
- Choice of circuits including 3 position and momentary
- Sealed version supplied complete with gaskets
- Panel seal version to IP67
- 6.3mm terminals
- Guard option

Terminal	Function	Actuator	Body	Options	
<div><div>C</div><div></div></div>	<div><div></div><div>Single Pole</div></div> <div><div>3900</div><div>ON - OFF</div><div></div></div> <div><div>3901</div><div>ON - OFF (momentary ON)</div><div></div></div> <div><div>3902</div><div>ON - OFF (momentary OFF)</div><div></div></div> <div><div>3910</div><div>ON - ON</div><div></div></div> <div><div>3911</div><div>ON - ON (momentary 1 side)</div><div></div></div> <div><div>3920</div><div>ON - OFF - ON µ</div><div></div></div> <div><div>3921</div><div>ON - OFF - ON µ (momentary 1 side)</div><div></div></div> <div><div>3922</div><div>ON - OFF - ON µ (momentary 2 sides)</div><div></div></div>	<div><div></div><div>Double Pole</div></div> <div><div>3950</div><div>ON - OFF</div><div></div></div> <div><div>3951</div><div>ON - OFF (momentary ON)</div><div></div></div> <div><div>3952</div><div>ON - OFF (momentary OFF)</div><div></div></div> <div><div>3960</div><div>ON - ON</div><div></div></div> <div><div>3961</div><div>ON - ON (momentary 1 side)</div><div></div></div> <div><div>3970</div><div>ON - OFF - ON µ</div><div></div></div> <div><div>3971</div><div>ON - OFF - ON µ (momentary 1 side)</div><div></div></div> <div><div>3972</div><div>ON - OFF - ON µ (momentary 2 sides)</div><div></div></div>	<div><div>A</div><div></div><div>Metal Metal toggle finish is nickel plate</div></div> <div><div>B</div><div></div><div>Metal Metal toggle finish is nickel plate</div></div> <div><div>D</div><div></div></div> <div><div>E</div><div></div><div>Metal toggle finish is nickel plate</div></div> <div><div>F</div><div></div><div>Metal toggle finish is nickel plate</div></div>	<div><div>A</div><div>Single pole Thread: 15/32" x 32TPI </div></div> <div><div>E</div><div>Panel sealed, single pole Thread: 15/32" x 32TPI </div></div> <div><div>A</div><div>Double pole, without barrier Thread: 15/32" x 32TPI </div></div> <div><div>B</div><div>Double pole, with barrier Thread: 15/32" x 32TPI </div></div> <div><div>F</div><div>Panel sealed, double pole, with terminal barrier Thread: 15/32" x 32TPI </div><div>Switches with F toggles have double pole bodies, regardless of circuit</div></div> <div><div>G</div><div>Panel sealed, double pole, without terminal barrier Thread: 15/32" x 32TPI </div></div>	<div><div>Neck Seal M539 Actuator is visible</div><div></div></div> <div><div>Cover M1080</div><div></div><div>Covers have internal nylon nuts</div></div> <div><div>M1080-2</div><div></div><div>Covers have internal metal hex nuts</div></div> <div><div>Fixing nuts Nickel plated brass are supplied</div><div></div></div> <div><div>Knurled Front nut Panel thickness 4.0 with backnut</div></div> <div><div>Plate P236 Plate SP or DP</div><div></div></div>

Approvals and specifications

UL/CSA Ratings 3901, 3902, 3920, 3921, 3922
16A, 277Vac
1 HP, 250Vac

7A, 72Vdc
14A, 36Vdc

3910, 3901, 3952, 3960, 3961, 3970, 3971, 3972
16A, 277Vac
1 HP, 250Vac
1/2 HP, 125Vac
7A, 72Vdc
14A, 36Vdc

3900, 3950
20A, 277Vac
1 HP, 250Vac
1/2 HP, 125Vac
7A, 72Vdc
14A, 36Vdc

ENEC Ratings
3900, 3901, 3902, 3950, 3952, 3960, 3961
16(4)A 250Vac

3910, 3911, 3920, 3921, 3922, 3951, 3970, 3972
10 4)A 250Vac


Approvals and ratings vary with function.
3mm contact gap except where marked μ .

* CSA approval for A and B bodies only

Dimensions mm) * Indicates ON position (for ON - OFF switches)


Single pole

(C terminals shown)




Double pole

(C terminals shown with barrier)



Toggle Switch - sealed version

BE and BF types



Guard TG1-RED



Examples



C3900BE - - -




C3920BA - - -



C3950BF - - -



C3972BB - - -









































Key Features

- Nylon toggle switches
- Ratings up to 20A, 250V ac
- Single and double pole
- Wide choice of terminals
- Choice of circuit options including 3 position
- Flat & round actuator options

Approvals and specifications

- 16(4)A 250Vac T85
- UL 20A 250Vac Non Ind (Single pole)
- UL 16A 250Vac Non Ind (Double pole)
- UL CSA (2 pos types) 250Vac 1hp, 125Vac 1/2hp
- UL CSA (3 pos types) 250Vac 1/2hp, 125Vac 1/4hp
- CSA 16A 250Vac Non Ind
- UL 85°C, file E45221, CSA file LR10990
- UL and CSA N/A on momentary types
- Selective "A, B, C" and "OFF, A, A+B" circuits at 5 amp also available.
- 3mm contact gap except where marked μ .


Terminal	Function	Actuator	Body	Options	
 C	 Single Pole 1700 ON - OFF 	 Double Pole 1750 ON - OFF 	 H	O Single pole Thread: 15/32" x 32TPI Keyway  10.0 12.2	Neck Seal M539 Material - Nitrile (H & R Actuators) Actuator visible 
 H	 Single Pole 1710 μ ON - ON 	 Double Pole 1760 μ ON - ON 		O Double Pole Thread: 15/32" x 32TPI Keyway  10.0 19.2  Ø12.7 1.3 11.1	Cover M1080 Material - EPDM (R Actuator only) 
 K	 Single Pole 1720 μ ON - OFF - ON 	 Double Pole 1770 μ ON - OFF - ON 	 R		Cover M531 Material - PVC (R Actuator only) Covers have internal nylon nuts 
 T	 Single Pole 1720 μ ON - OFF - ON 	 Double Pole 1770 μ ON - OFF - ON 			Fixing nuts (Standard is M506 & T92) T5 Hex brass M506 Hex nylon 
 X	 Single Pole 1721 μ ON - OFF - ON μ (momentary 1 side) 	 Double Pole 1770 μ ON - OFF - ON 			T92 Knurled brass - slotted  2.6 M279 Knurled nylon  4.1
	1722 ON - OFF - ON μ (momentary 2 sides) 		The switch is on between centre terminals (2 & 5) and the terminals over which the lever is positioned.		Plate P236 Plate SP or DP 

Dimensions

mm) * Indicates ON position (for ON - OFF switches)

Single pole


(C terminals shown)




Optional
F00232PAAA
plate SP or DP

Double pole


(C terminals shown)



Without barrier



With barrier



Examples



C1700R - -



C1700H - -



C1760R - -



C1750H - -