



THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.



ORDERING CODE: F C E 1 7 - E 0 9 P A - 4 4 0 G

SERIES
FCE17=FILTERED D-SUB, RoHS


SIZE/NUMBER OF CONTACTS
E09, A15, B25, OR C37

CONNECTOR STYLE
P=PIN
S=SOCKET

TERMINATION TYPE
A=.318" [8.08] FOOTPRINT



CAPACITANCE SCHEMATIC
FOR EACH POSITION



REVISIONS			
REV	ECN, ERN NO.	DATE	APPRD.
G	PRODUCT DRAWING (EAR 14218)	TBD	K.L.

CONTACT FINISH/GOLD THICKNESS
NO DIGIT=STANDARD 15 MICROINCHES
[0.38 MICRONS] GOLD ON
MATING AREA
G=50 MICROINCHES [1.27 MICRONS]
GOLD ON MATING AREA

MODIFIER
O=STANDARD

FILTER CAPACITANCE
D=50 pF 5=1000 pF
B=100 pF 7=1200 pF
O=180 pF 6=1300 pF
T=220 pF J=1500 pF
F=330 pF E=2200 pF
L=380 pF 9=5600 pF
1=470 pF 8=47000 pF
2=680 pF N=NO FILTERS
4=820 pF
REFER TO AMPHENOL CATALOGUE FOR
FILTER PERFORMANCE CHARACTERISTICS

MOUNTING
2=.120 [3.05] DIA THROUGH HOLE
3=#4-40 UNC SELF-LOCKING THREAD
4=#4-40 UNC THREAD
6=M3 x 0.5 THREAD
E=CODE 4 MOUNTING WITH #4-40
UNC HEX JACK SOCKETS SUPPLIED.
F=#4-40 UNC FIXED ROUND JACK SOCKET

NOTES:

- MATERIALS: ALL MATERIALS ARE RoHS COMPLIANT.
 - SHELL: STEEL, TIN PLATED
 - CONTACTS: PHOSPHOR BRONZE, PLATED WITH GOLD OVER 50μ" [1.27 MICRONS] MINIMUM NICKEL IN THE MATING AREA AND 100μ" [2.54 MICRONS] MINIMUM MATTE TIN ON THE TAILS.
 - INSULATOR: ENGINEERING THERMOPLASTIC, GLASS REINFORCED, UL FLAMMABILITY RATING 94V-0, COLOUR: BLACK
 - BOARDLOCK: COPPER ALLOY, TIN PLATED
 - MOUNTING HARDWARE, STEEL OR COPPER ALLOY, TIN OR NICKEL PLATED.
- CONTACT RESISTANCE: 15 MILLIOHMS MAXIMUM
- INSULATION RESISTANCE: 3000 MEGOHMS MINIMUM
- CURRENT RATING: 5 AMPS MAXIMUM
- OPERATING TEMPERATURE: -40°C TO 85°C
- TOLERANCE UNLESS INDICATED OTHERWISE: ±.005 [0.13]

SIZE	STYLE	A±.015 [0.38]	B±.005 [0.13]	C±.005 [0.13]	D±.005 [0.13]	E BSC.
E09	PIN	1.213 [30.81]	-----	.666 [16.92]	.984 [24.99]	.432 [10.97]
	SOCKET	-----	.643 [16.33]	-----	-----	-----
A15	PIN	1.541 [39.14]	-----	.994 [25.25]	1.312 [33.32]	.756 [19.20]
	SOCKET	-----	.971 [24.66]	-----	-----	-----
B25	PIN	2.088 [53.04]	-----	1.534 [38.96]	1.852 [47.04]	1.304 [33.12]
	SOCKET	-----	1.511 [38.38]	-----	-----	-----
C37	PIN	2.729 [69.32]	-----	2.182 [55.42]	2.500 [63.50]	1.956 [49.68]
	SOCKET	-----	2.159 [54.84]	-----	-----	-----

DRAWN K. LAMBIE	DATE APR08/05
DESIGNED	
CHECKED	
I. E. APPRD.	
Q. A. APPRD.	
DWG. APPRD.	
ENG. REL. NO.	
REF. EAR #12701	
DIMENSIONS ARE IN INCHES [mm]	CODE ID. NO. 03554



Amphenol Canada Corp.

FCE17 SERIES FILTERED D-SUB CONNECTOR, PIN & SOCKET, RIGHT ANGLE .318 [8.08] F/P, PLASTIC MOUNTING BRACKET & BOARDLOCK, RoHS COMPLIANT

DWG C	DRAWING NO. P-FCE17-XXXXA-XX0X	REV. G
SCALE 3/1	WT. -----	SURF. -----
SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[FCE17-C37PA-410](#) [FCE17-C37SA-410](#) [FCE17E09PAE10](#) [FCE17-A15SA-440](#) [FCE17-C37SA-440](#) [FCE17-E09PA-440](#) [FCE17-B25SA-410](#) [FCE17-A15PA-490](#) [FCE17-B25SA-490](#) [FCE17-E09PA-490](#) [FCE17-E09PM-490](#) [FCE17-A15SA-450](#) [FCE17-A15SM-210](#) [FCE17-B25PA-440](#) [FCE17-E09PA-410](#) [FCE17-C37PA-440](#) [FCE17-E09SA-440](#) [FCE17-A15PM-210](#) [FCE17-E09PM-240](#) [FCE17-E09SM-290](#) [FCE17-B25PA-490](#) [FCE17-E09SA-450](#) [FCE17-E09SA-490](#) [FCE17-B25SA-440](#) [FCE17-E09SA-410](#) [FCE17-A15PA-440](#) [FCE17-C37PA-490](#) [FCE17-A15SA-EE1](#) [FCE17B25SA25B](#) [FCE17E09PA21B](#) [FCE17A15SA280](#) [FCE17A15PA6D0](#) [FCE17E09PA480](#) [FCE17B25SA280](#) [FCE17E09SA6D0](#) [FCE17C37SA60B](#) [FCE17E09SA210](#) [FCE17C37PA6E0](#) [FCE17C37PA600](#) [FCE17E09PA200](#) [FCE17E09PA6EB](#) [FCE17E09SA65B](#) [FCE17C37PA49B](#) [FCE17A15SA4EB](#) [FCE17B25PA48B](#) [FCE17A15PA690](#) [FCE17E09SA29B](#) [FCE17A15SA29B](#) [FCE17A15PA2DB](#) [FCE17C37PA24B](#) [FCE17C37PA61B](#) [FCE17E09PA44B](#) [FCE17A15PA480](#) [FCE17A15PA44B](#) [FCE17C37PA60B](#) [FCE17B25PA21B](#) [FCE17C37SA20B](#) [FCE17C37SA45B](#) [FCE17C37SA480](#) [FCE17A15SA4D0](#) [FCE17E09PA210](#) [FCE17B25SA64B](#) [FCE17E09SA6EB](#) [FCE17B25PA650](#) [FCE17C37SA2EB](#) [FCE17C37SA610](#) [FCE17C37SA25B](#) [FCE17C37PA6EB](#) [FCE17B25PA450](#) [FCE17A15PA4D0](#) [FCE17B25SA450](#) [FCE17B25SA240](#) [FCE17A15PA280](#) [FCE17B25PA2DB](#) [FCE17B25PA680](#) [FCE17B25SA610](#) [FCE17A15PA610](#) [FCE17A15PA25B](#) [FCE17C37PA44B](#) [FCE17B25SA4DB](#) [FCE17A15SA480](#) [FCE17A15SA21B](#) [FCE17A15SA210](#) [FCE17B25SA21B](#) [FCE17B25SA650](#) [FCE17B25PA4DB](#) [FCE17A15PA21B](#) [FCE17C37SA6DB](#) [FCE17C37SA250](#) [FCE17B25PA600](#) [FCE17E09SA60B](#) [FCE17A15PA250](#) [FCE17C37SA48B](#) [FCE17B25PA65B](#) [FCE17E09PA2D0](#) [FCE17E09PA610](#) [FCE17E09PA25B](#) [FCE17E09SA68B](#) [FCE17A15PA69B](#) [FCE17C37SA240](#)