





REV.	DATE	DESCRIPTION
NC	05/24/05	INITIAL RELEASE
A	10/11/99	UPDATE DRAWING / MODIFY FERRULE
B	07/31/01	MODIFY FERRULE
C	08/10/05	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex			
8					DRAWN	G.R.S.	08/10/05					
7					CHECKED			PART DESCRIPTION BNC CRIMP PLUG (58T BELDEN 89907)				
6					ISSUED							
5					SHEET	1 OF 1		PART NO. 112124				
4	FERRULE	BRASS	NICKEL		1							
3	CONTACT PIN	BRASS	GOLD		1			DWG. NO. 112124.DWG				
2	INSULATOR	DELRIIN	NATURAL		1							
1	BODY	BRASS	NICKEL	1			REV. C	SIZE A	SCALE NA			
DESCRIPTION				MATERIAL	FINISH	QTY	CAD FILE C:/112/112124.DWG					