

T8 Lamps

U-Bent Rapid Start Fluorescent Lamps T8 Medium Bipin with 6" long spacing (212)

Nominal Lamp Watts	Product Number 046677-	Ordering Code	Pkg. Qty. •	Description	Nom. Length (In.)	Avg. Life Hrs. Rapid Start (202, 224)	Approx. Initial Lum. (203, 204)	Design Lumens (208)	CRI
32	(E) \$ 37897-6	FB32T8/TL830/6/ALTO	20	TL 80, 3000K	22 7/16	20,000	2800	2535	85
	(E) \$ 37900-8	FB32T8/TL835/6/ALTO	20	TL 80, 3500K	22 7/16	20,000	2800	2535	85
	(E) \$ 37902-4	FB32T8/TL841/6/ALTO	20	TL 80, 4100K	22 7/16	20,000	2800	2535	85
	(E) \$ 37880-2	FB32T8/TL850/6/ALTO	20	TL 80, 5000K	22 7/16	20,000	2750	2500	84
	(E) \$ 37892-7	FB32T8/TL730/6/ALTO	20	TL 70, 3000K	22 7/16	20,000	2650	2370	75
	(E) \$ 37893-5	FB32T8/TL735/6/ALTO	20	TL 70, 3500K	22 7/16	20,000	2650	2370	75
	(E) \$ 37888-5	FB32T8/TL735/6/ALTO/UPC	20	TL 70, 3500K	22 7/16	20,000	2650	2370	75
	(E) \$ 37894-3	FB32T8/TL741/6/ALTO	20	TL 70, 4100K	22 7/16	20,000	2650	2370	75
	(E) \$ 37889-3	FB32T8/TL741/6/ALTO/UPC	20	TL 70, 4100K	22 7/16	20,000	2650	2370	75
	(E) \$ 37882-8	FB32T8/TL750/6/ALTO	20	TL 70, 5000K	22 7/16	20,000	2600	2325	75

Instant Start Fluorescent Lamps T8 Single Pin

Nominal Lamp Watts	Product Number 046677-	Ordering Code	Pkg. Qty. •	Description	Nom. Length (In.)	Average Life Hours	Approx. Initial Lum. (203, 204)	Design Lumens (208)	CRI
59	(E) \$ 34457-2	F96T8/TL830	24	TL 80, 3000K	96	15,000	5900	5490	85
	(E) \$ 34460-6	F96T8/TL835	24	TL 80, 3500K	96	15,000	5900	5490	85
	(E) \$ 34462-2	F96T8/TL841	24	TL 80, 4100K	96	15,000	5900	5490	85
	(E) \$ 21479-1	F96T8/TL850	24	TL 80, 5000K	96	15,000	5780	5375	84
	(E) \$ 34453-1	F96T8/TL730	24	TL 70, 3000K	96	15,000	5700	5190	75
	(E) \$ 34455-6	F96T8/TL735	24	TL 70, 3500K	96	15,000	5700	5190	75
	(E) \$ 34456-4	F96T8/TL741	24	TL 70, 4100K	96	15,000	5700	5190	75
	(E) \$ 21477-5	F96T8/TL750	24	TL 70, 5000K	96	15,000	5580	5080	75

High Output Fluorescent Lamps T8 Recessed Double Contact (224)

Nominal Lamp Watts	Product Number 046677-	Ordering Code	Pkg. Qty. •	Description	Nom. Length (In.)	Average Life Hours	Approx. Initial Lumens (203, 204)	Design Lumens (208)	CRI
44	\$ 28299-6	F48T8/TL830/HO	24	TL 80, 3000K	48	18,000	4000	3600	85
	\$ 28306-9	F48T8/TL835/HO	24	TL 80, 3500K	48	18,000	4000	3600	85
	\$ 28309-3	F48T8/TL841/HO	24	TL 80, 4100K	48	18,000	4000	3600	85
	\$ 28268-1	F48T8/TL730/HO	24	TL 70, 3000K	48	18,000	3800	3420	75
	\$ 28273-1	F48T8/TL735/HO	24	TL 70, 3500K	48	18,000	3800	3420	75
	\$ 28282-2	F48T8/TL741/HO	24	TL 70, 4100K	48	18,000	3800	3420	75
55	\$ 28316-8	F60T8/TL830/HO	24	TL 80, 3000K	60	18,000	5050	4545	85
	\$ 28317-6	F60T8/TL835/HO	24	TL 80, 3500K	60	18,000	5050	4545	85
	\$ 28320-0	F60T8/TL841/HO	24	TL 80, 4100K	60	18,000	5050	4545	85
	\$ 28283-0	F60T8/TL730/HO	24	TL 70, 3000K	60	18,000	4800	4320	75
	\$ 28286-3	F60T8/TL735/HO	24	TL 70, 3500K	60	18,000	4800	4320	75
	\$ 28291-3	F60T8/TL741/HO	24	TL 70, 4100K	60	18,000	4800	4320	75

\$ — Energy Saving Product


(E) — This Bulb Meets US Federal Minimum Efficiency Standard

Footnotes located on page 78

□ — Features ALTO® Lamp Technology

■ — Highest Color Rendering Lamps (CRI ≥ 80)


□ — High Color Rendering Lamps (CRI 70–79)



T8 Medium Bipin U-Bent



T8 Single Pin



T8 Recessed D.C.