





THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE	(.0)	$\pm .030$
-----------	------	------------

TWO PLACE	(.00)	$\pm .015$
THREE PLACE	(.000)	$\pm .005$

THREE-PLATE	1.0007	±
ANGLES		±

WEIGHT 670 LB

10/10/2018 12:00 PM

CHARACTERISTICS

OPERATING FORCE ————— 2 LB MAX

RELEASE FORCE ———— 1/2 LB MIN

PRETRAVEL — — — — — .219 MAX

DIFFERENTIAL TRAVEL ——— .004 MAX

OVERTRAVEL ----- 219 MIN

DATE OF BIRTH: 07-07-1900

BASIC SWITCH REPLACEMENT BZ-2R/08-P7

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L96

15A 125, 250 OR 480 VAC
1/8 HP 125 VAC, 1/4 HP 250 VAC
1/2A 125 VDC, 1/4A 250 VDC



NOTES

1 - ROLLER LEVER BRACKET ASSEMBLY MAY BE SET IN ANY POSITION
AROUND AXIS OF PLUNGER

2 - 8-32 UNC X (.219) BINDER HEAD, COMBINATION, TERMINAL SCREWS
AND CUPWASHERS