







NOTE: ROHS COMPLIANT


TOLERANCE		
L < 20	±0.2	
20 ≤ L < 50	±0.3	
50 ≤ L < 100	±0.4	
100 ≤ L	±0.5	

REV.	DESCRIPTION/ECO NO.	DATE
	RELEASED AS CAD DRW.	9/25/01
A	CHNG PER SUPPLIERS SPEC.	4/3/07

CHARACTERISTICS		MIN	TYP	MAX
INPUT VOLTAGE: (vdc)		10.8	12.0	15.0
INPUT CURRENT: (ma)		115	135	155
OUTPUT VOLTAGE: (Vrms)		-	800	-
OUTPUT CURRENT (marms)		3.9	4.6	5.3
OUTPUT FREQUENCY: (kHz)		80	90	100
OPERATING TEMP: (CELSIUS)		0	25	50

BOARD PIN #	INPUT
1	+V (V in)
2	V (GND)
HV	V OUT
HG	OUT GND

M1 - INPUT CURRENT (I in)
M2 - INPUT VOLTAGE (V in)
M3 - OUTPUT CURRENT (I out)
M4 - OUTPUT VOLTAGE (V out)



METRIC		DIMENSIONS ARE IN MILLIMETERS	
THIRD ANGLE PROJECTION		TOLERANCE UNLESS OTHERWISE SPECIFIED	
1 PL +/- 0.2		2 PL +/- 0.2	
ANGLE +/- 0		DATE	
DRAWN BY L. WENGSTROM		DATE	DATE
L.R.		4/3/07	4/3/07
- CAD DRAWING -		SCALE	SCALE
MANUAL REVISIONS NOT PERMITTED		NONE	NONE

JKL COMPONENTS CORPORATION			
12V CCFL POWER SUPPLY			
DRAWING NO.		BXA-12577	
FSCM NO.		55335	
NO.		4/3/07	
RELEASED		9/25/01	
DATE		4/3/07	
REV.		A	
NO.		A	
SHEET		OF	