

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

90814-3910

Status:

Active

Overview:

Picoflex®

Description:

1.27mm Pitch Picoflex® PF-50 SMT Header with PCB Pegs, Vertical, Low Profile, Surface Mount, Gold (Au) Plated, 10 Circuits, Natural

Documents:

3D Model

Drawing (PDF)

Product Specification PS-99020-0011 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Application Tooling Part Link

Comments

Overview

Product Name

PCB Headers

90814

Signal, Wire-to-Board

690081070

Low Profile

Picoflex®

Picoflex®

Physical

Breakaway

Circuits (Loaded)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Glow-Wire Compliant

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Resin

Number of Rows

Orientation

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

No

10

Natural

100

No

94V-0

No

No

None

Yes

Brass

Gold

High Temperature Thermoplastic

1

Vertical

Yes

Yes

1.60mm

Adhesive Tape on Reel

1.27mm

1.27mm

0.762µm

0.102µm

Yes

Yes

No

No

Yes

-40°C to +105°C

Surface Mount

Electrical

Current - Maximum per Contact

2.4A




image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

90814Series

Mates With

90327 IDT Connector

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Tool (Plastic) for 4-26 Circuit	0690081070

Voltage - Maximum	250V AC/DC
-------------------	------------

Solder Process Data

Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	230

Material Info

Reference - Drawing Numbers

Product Specification	PS-99020-0011
Sales Drawing	SDA-90814

This document was generated on 04/04/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION