



10	9	8	7	6	5	4	3	2	19139
MATERIAL NUMBER	ALTERNATE NUMBER	STUD SIZE	"S"	"W"	PACKAGING				
191390009	AA-834-04	4	.119/(3.02)	.291 (7.39)	LOOSE PIECE				
191390011	AA-834-06	6	.146/(3.71)	.291 (7.39)					
191390013	AA-834-08	8	.173/(4.39)	.291 (7.39)					
191390015	AA-834-10	10	.198/(5.03)	.291 (7.39)					
191390016	AA-838-04	4	.119/(3.02)	.245 (6.23)					
191390018	AA-838-06	6	.146/(3.71)	.245 (6.23)					
191390010	AA-834-04T	4	.173/(4.39)	.291 (7.39)	TAPE MOUNTED				
191390012	AA-834-06T	6	.146/(3.71)	.291 (7.39)					
191390014	AA-834-08T	8	.173/(4.39)	.291 (7.39)					
191390017	AA-838-04T	4	.119/(3.02)	.245 (6.23)					
191390019	AA-838-06T	6	.146/(3.71)	.245 (6.23)					



- NOTES:
1. MATERIAL: COPPER .028 THICK
PLATING: MATTE TIN
 2. FERRULE: TIN-PLATED BRASS
 3. INSULATION: RED NYLON
 4. MWID=MAXIMUM WIRE INSULATION DIA.
 5. PARTS ARE ROHS COMPLIANT.

CUSTOMER DRAWING

CORRECT TOLERANCES EC NO: IPG2012-0575 DRW:NETHRODAHL 2012/04/16 CHKD: JMACNEIL 2012/04/16 APPR: JMACNEIL 2012/04/19 A1	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION				
					DRAWN BY EDB	DATE 2000/11/17	TITLE SPADE TONGUE TERMINAL AVIKRIMP -800 SERIES 22-18 AWG molex						
					CHECKED BY HEB	DATE 2000/11/17							
					APPROVED BY DATE								
					MATERIAL NO.							DOCUMENT NO. SD-19139-001	SHEET NO. 1 OF 1
					SEE CHART								
			ANGULAR ±---°		SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										