






CIRCUIT: 2P: SPST
CONTACT CONFIGURATION
ON-OFF

SWITCH FUNCTION		
POS. 1	POS. 3	
ON	OFF	
1-2	OPEN	



RECOMMEND PANEL MOUNTING



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: 0.0 ± 0.4
 0.00 ± 0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 16A, 125VAC, 10A, 250VAC UL&CUL APPROVED
10A 125VAC, 6A 250V AC VDE APPROVED
5. CONTACT RESISTANCE: 50m ohm max.
6. INSULATION RESISTANCE: DC 500V 100M ohm min.
7. DIELECTRIC STRENGTHS: AC 1500V 1 minute
8. OPERATING TEMP.: -20°C to 85°C
9. ▲ DENOTES CRITICAL PARAMETER.
10. 2002/95/EC (ROHS) COMPLIANT
11. PACKAGE: BAG/1,000 PIECES PER

TITLE			
RR3112ABL KREDNEFD			
E-SWITCH			
A	16968	RELEASED FOR PRODUCTION	2/7/07
REV.	ECN No.	DESCRIPTION	DATE
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE			
2:1			
DATE			
2/7/07			
DR			
TN			
DWG			
F130427			
REV			
A			